



L885/6



L895/8



L945/5



Part No.	Emitting Color + Material	λ D (nm)	Lens Type	Iv (mcd) @ 10mA *20mA		Viewing Angle	Dimension
				Min.	Typ.		
L885/6IDT	GaAsP/GaP	625	red diffused	5	10	120°	10mm x 16mm
L885/6GDT	GaP	568	green diffused	5	10	120°	
L885/6YDT	GaAsP/GaP	588	yellow diffused	5	10	120°	
L885/6SRDT	GaAlAs	640	red diffused	*20	*60	120°	
L895/8IDT	GaAsP/GaP	625	red diffused	5	10	120°	10mm x 22mm
L895/8GDT	GaP	568	green diffused	5	10	120°	
L895/8YDT	GaAsP/GaP	588	yellow diffused	5	10	120°	
L895/8SRDT	GaAlAs	640	red diffused	*20	*60	120°	
L945/5HD	GaP	660	red diffused	0.5	1	110°	1mmx5mm 5 Elements
L945/5GD	GaP	568	green diffused	0.8	2	110°	
L945/5YD	GaAsP/GaP	588	yellow diffused	0.8	2	110°	

NOTES :

- All dimensions are in millimeters (inches)
- Tolerance is ± 0.25 mm (0.01") unless otherwise noted.