

MLCC with Dipped Radial Lead

Product Top Page

Search by Part No.

Search by Characteristics

Cross Reference

Catalog

Tech Note

FAQ

FK18X5R1E474KR006



Applications



Commercial Grade

Feature

General

General (Up to 50V)

Series


FK

Status



Production (Not Recommended for New Design)

Recommended Alternate Part No. : [FG18X7R1H474KRT06](#)



Images are for reference only and show exemplary products.

PDF file of this page



Contact



Documents



Catalog



Specification



RoHS Certificate



SVHC/REACH Certificate

Size

Length(L)	4.00mm Max.
Width(W)	5.50mm Max.
Thickness(T)	2.50mm Max.
Lead Gap(F)	2.50mm +0.50,-0.20mm
Lead Diameter(d)	0.50mm +0.10,-0.03mm

Electrical Characteristics

Capacitance	470nF ±10%
Rated Voltage	25VDC
Withstanding Voltage	62.5VDC
Temperature Characteristic	X5R(±15%)
Dissipation Factor (Max.)	5%
Insulation Resistance (Min.)	1063MΩ

Other

Soldering Method	Wave (Flow) Iron Soldering
Lead Length / Package Type	Taping
AEC-Q200	No
Package Quantity	2000pcs

Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)

Impedance

no data available

Capacitance

no data available

Change settings

DC Bias Characteristic

no data available

Change settings

Change settings

Temperature Characteristic

no data available

Change settings

Products

- » Selection Guide » Search by Part No. » Search by Characteristics » Distributor Inventory Check
- » Capacitors

» Inductors (Coils)

» EMC Components

» RF Components and Modules

» Voltage / Current / Temperature Protection Devices

» Sensors and Sensor Systems

» Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones

» Transformers

» Ferrites and Accessories

» Noise Suppressing / Magnetic Sheet
- » Anechoic Chambers and Radio Wave Absorbers

» Power Supplies

» Magnets

» Flash Storages

» Wireless Power Transfer

» FA Systems

» Transparent Conductive Film

» Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)

» Solar Cells

» Biosensor

- Application Guides
- Technical Support
- Tech Library
- Environment
- Contact
- News
- Home

-  About TDK
-  TDK Worldwide