



Technical drawing of a U-shaped part with dimensions:

- Top Left Dimension:** $2.08^{+0.25}_{-0.13}$
- Bottom Left Dimension:** $\begin{bmatrix} .082^{+.010} \\ -.005 \end{bmatrix}$ TYP
- Top Right Dimension:** $2.41^{+0.13}_{-0.25}$
- Bottom Right Dimension:** $\begin{bmatrix} .095^{+.005} \\ -.010 \end{bmatrix}$

10	OBSOLETE	SMALL PACK	9	BRASS	2-66104-9 OR 3-66104-0	2-66105-0
		STANDARD	9	BRASS	2-66104-9 OR 3-66104-0	1-66105-9
		SMALL PACK	1	BRASS	66104-4	1-66105-8
	OBSOLETE	SMALL PACK	4	BRASS	66104-3	1-66105-7
		SMALL PACK	2	BRASS	66104-2	1-66105-6
		SMALL PACK	3	BRASS	66104-1	1-66105-5
		STANDARD	8	BRASS	2-66104-6	1-66105-4
		STANDARD	1	PHOSPHOR BRONZE	2-66104-3	1-66105-3
	OBSOLETE	STANDARD	2	PHOSPHOR BRONZE	2-66104-2	1-66105-2
		STANDARD	5	BRASS	1-66104-6	1-66105-0
STANDARD		1	BRASS	66104-4	66105-4	
STANDARD		4	BRASS	66104-3	66105-3	
STANDARD		2	BRASS	66104-2	66105-2	
OBSOLETE	STANDARD	3	BRASS	66104-1	66105-1	
	PACKAGING TYPE	BODY FINISH	MATERIAL	STRIP P/N REF	PART NO	

A2	00779	C-66105	—
SCALE		SHEET	REV