




Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers >

NextGen & NextGen Plus MCON 1.2 Locking Lance Accessories



Number of Positions: 2

Primary Product Color: **Black**

Protection & Strain Relief Accessory Type: **Wire Dress Cover**

Primary Product Material: **PA**

Cable Exit Angle: **180 °**

[All NextGen & NextGen Plus MCON 1.2 Locking Lance Accessories \(5\)](#)

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Wire Dress Cover

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Color	Black
Primary Product Material	PA
Cable Exit Angle	180 °

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	150 °C[302 °F]
-----------------------------	----------------



Operating Temperature Range

-40 – 150 °C[-40 – 302 °F]

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # 2373785-2 MCON,CABLE ASSY,M TO F, 1000MM	 TE Part # 2373785-5 MCON,CABLE ASSY,M TO F, 5000MM	 TE Part # 2373781-2 MCON,CABLE ASSY,F TO F, 1000MM	 TE Part # 2373785-3 MCON,CABLE ASSY,M TO F, 1500MM
 TE Part # 2362353-3 ENETSEAL, F TO F, 1500MM	 TE Part # 2362354-3 ENETSEAL, M TO F, 1500MM	 TE Part # 2362354-5 ENETSEAL, M TO F, 5000MM	 TE Part # 2292906-3 2POS,MCON 1.2,REC HSG ASSY,SLD, COD C,.
 TE Part # 2278384-2 SGM NGC CABLE	 TE Part # 2292937-3 2POS,1.2X0.6,TAB HSG ASSY,SLD, COD C	 TE Part # 2373785-4 MCON,CABLE ASSY,M TO F, 3000MM	 TE Part # CAT-N14-RC4812 48V Ready 1.2mm Sealed Connectors
 TE Part # 2362353-2 ENETSEAL, F TO F, 1000MM	 TE Part # 2362354-4 ENETSEAL, M TO F, 3000MM	 TE Part # 2373781-5 MCON,CABLE ASSY,F TO F, 5000MM	 TE Part # 2373781-3 MCON,CABLE ASSY,F TO F, 1500MM
 TE Part # 2362354-2 ENETSEAL, M TO F, 1000MM	 TE Part # 2360014-1 SGM CVG BSM CABLE	 TE Part # 2299137-1 SGM NGC PLUS CABLE	 TE Part # 2292906-1 2POS,MCON 1.2,REC HSG ASSY,SLD, COD A

Also in the Series | enetSEAL+




Automotive Housings(117)



Automotive Signal & Power Connector Housings(116)



Infotainment & Multimedia Cable Assemblies(8)



Other Automotive Connector Accessories(1)

Also in the Series | MCON Interconnection System




Automotive Connector Caps & Covers (43)



Automotive Housings(117)




Automotive Signal & Power Headers(4)



Automotive Terminals(23)



Connector Seals & Cavity Plugs(12)




Other Automotive Connector Accessories(1)


Customers Also Bought



TE Part #829131P051
ES2000-NO.1-C1-0-40MM



TE Part #925324-1
FF 250 REC HSG 1P NYLON BLACK



TE Part #1612108-4
025/040 CAVITY PLUG



TE Part #1658539-5
PIN CONT DUPL PLT STRIP HD-20



TE Part #1718348-1
MCON 1.2 CB TAB STC SN



TE Part #2029185-1
CMNL SKT W/INDENTED SIDES



TE Part #2040594-3
SEAL CAP HSG 4P, AMPSEAL16 SEA



TE Part #2292797-3
AS16,PLUG BACKSHELL KIT,ST,02P, NC08



Documents

Product Drawings

MCON WIRE DRESS, 2P PLUG, STRAIGHT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2272168-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2272168-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2272168-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

1.2-mm MCON Wire Dress Cover

English