

ECF504-C3



ECF504-SC3



ECF504-C5






ECF504-SC5E



ECF504-C6




ECF504-SC6

PR175F504B-C3
PR175F504B-C5
PR175F504B-C6PR175F504B-SC3
PR175F504B-SC5
PR175F504B-SC6PR35F504B-C3
PR35F504B-C5
PR35F504B-C6PR35F504B-SC3
PR35F504B-SC5
PR35F504B-SC6

PR175F504B



PR35F504B



Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------


Premium Panel Mounted Modular Coupler Kits - Category 3, 5E & 6 - Shielded & Unshielded

These unique coupler kits allow panel mounting in virtually any panel thickness. A solid die-cast metal mounting frame provides secure mounting and reliable grounding. Kits include a snap-in coupler, mounting frame and two 4-40 machine screws.

ECF504-C3	Category 3 Unshielded RJ45 (8x8) Deluxe Panel Coupler Kit	6.45	5.93	4.90	4.90	4.39
ECF504-SC3	Category 3 Shielded RJ45 (8x8) Deluxe Panel Coupler Kit	8.45	7.77	7.10	6.42	5.75
ECF504-C5	Category 5E Unshielded RJ45 (8x8) Deluxe Panel Coupler Kit	9.45	8.69	7.94	7.18	6.43
ECF504-SC5E	Category 5E Shielded RJ45 (8x8) Deluxe Panel Coupler Kit	11.45	10.53	9.62	8.70	7.79
ECF504-C6	Category 6 Unshielded RJ45 (8x8) Deluxe Panel Coupler Kit	10.45	9.61	8.78	7.94	7.11
ECF504-SC6	Category 6 Shielded RJ45 (8x8) Deluxe Panel Coupler Kit	12.45	11.45	10.46	9.46	8.47


TIP: How to install a premium ECF Kit

STEP 1



Secure frame in specified opening with supplied hardware and align coupler in proper orientation to the opening.

STEP 2



Seat bottom retainer and pivot coupler upward while depressing upper retainer.

STEP 3



Coupler fully seated.


Telecom and Network Grade Patch Panels

These 19" Panels feature L-com's exclusive ECF series flange mounted feed-thru couplers. These couplers are available in Category 3, 5E, or 6 and either shielded or non-shielded styles. The ECF series couplers are unique in that they use 2 4-40 screws to firmly attach the connector flange to the rack panel. The panels have a powder coat black finish for durability and each port is numbered to simplify cable organization and tracking. Both 16 and 32 port versions are available.

PR175F504B-C3	1.75" Panel with 16 Category 3 Couplers	119.84	110.25	100.67	91.08	CALL
PR175F504B-SC3	1.75" Panel with 16 Category 3 Shielded Couplers	149.95	137.95	125.96	113.96	CALL
PR35F504B-C3	3.5" Panel with 32 Category 3 Couplers	219.95	202.35	184.76	167.16	CALL
PR35F504B-SC3	3.5" Panel with 32 Category 3 Shielded Couplers	274.95	252.95	230.96	208.96	CALL
PR175F504B-C5	1.75" Panel with 16 Category 5E Couplers	159.95	147.15	134.36	121.56	CALL
PR175F504B-SC5	1.75" Panel with 16 Category 5E Shielded Couplers	199.95	183.95	167.96	151.96	CALL
PR35F504B-C5	3.5" Panel with 32 Category 5E Couplers	299.95	275.95	251.96	227.96	CALL
PR35F504B-SC5	3.5" Panel with 32 Category 5E Shielded Couplers	369.95	340.35	310.76	281.16	CALL
PR175F504B-C6	1.75" Panel with 16 Category 6 Couplers	179.95	165.55	151.16	136.76	CALL
PR175F504B-SC6	1.75" Panel with 16 Category 6 Shielded Couplers	209.95	193.15	176.36	159.56	CALL
PR35F504B-C6	3.5" Panel with 32 Category 6 Couplers	329.95	303.55	277.16	250.76	CALL
PR35F504B-SC6	3.5" Panel with 32 Category 6 Shielded Couplers	389.95	358.75	327.56	296.36	CALL
PR175F504B	1.75" Panel, 16 ECF Style Cutouts, Black	29.95	28.15	26.36	24.56	22.76
PR35F504B	3.50" Panel, 32 ECF Style Cutouts, Black	34.95	32.85	30.76	28.66	26.56

TIP: What is the difference between Category 5E and Category 6 100 Ohm UTP?

The new Category 6 Standard adopted in mid 2002 extended key parameters over 5E specifications. The additional headroom is intended to provide quality transmission at higher data rates required by emerging applications. As the chart indicates, the most prominent difference is the frequency at which the key parameters are measured. The jump from 100 to 250MHz places a great deal of emphasis on component quality as well as installation techniques. This improvement is commonly noticed by the increased pair twisting and staggering of twisted pairs.



	Category 5E	Category 6
Frequency	100 MHz	250MHz
Attenuation	22db	19.8db/100M @ 100 MHz 32.8db/100M @ 250 MHz
Return Loss	19db	19db @ 100 MHz 15.6db @ 250 MHz
Delay Skew	45ns	45ns
Near End Crosstalk (NEXT)	35.3db	44.3db @ 100 MHz 38.3db @ 250 MHz
Power Sum Near End Crosstalk (PS-NEXT)	32.3db	42.3db @ 100 MHz 36.3db @ 250 MHz
Equal Level Far End Crosstalk (ELFEXT)	23.8db	27.8db @ 100 MHz 19.8db @ 250 MHz
Power Sum Equal Level Far end Crosstalk (PS-ELFEXT)	20.8db	24.8db @ 100 MHz 16.8db @ 250 MHz