

6

5

4

3




2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/22/11	



FERRULE	BRASS	GOLD
SPIGOT	BRASS	GOLD
INSULATOR	TEFLON	
PIN	BRASS	GOLD
BODY	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 75 ohms

Frequency range: 0-4 GHz

Working Voltage: 335 VRMS max.

Dielectric Withstanding Voltage: 1000 VRMS min.

Contact Resistance: 6 Milliohms max. (Center Contact)
2.5 Milliohms max. (Outer Contact)

Insulator Resistance: 1000 Megohms min.

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	AY	12/22/11
CHECKED	NP	12/22/11
APPROVED		

ADAM TECH909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710TITLE
SMB MALE R/A, 75 OHMS, GOLD PLATED

SIZE X	PART NO. RF3-03-T-03-75-G	REV. -
REF: S00049T	SCALE: NTS	SHEET 1 OF 1

6

5

4

3

2

1