
Part Number : 5031492200
Product Description : CLIK-Mate Plug Housing, 1.50mm Pitch, Dual Row, Positive Lock, 22 Circuits, Natural
Series Number : 503149
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

5031492200_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

5031492200.dxf

Specifications

AS-503149-001-001.pdf

SPK-503149-001-001.pdf

5031490000-PS-000.pdf

5031491000-PS-000.pdf

5031491001-PS-000.pdf

5031491002-PS-000.pdf

5031491003-PS-000.pdf

PS-505406-001-001.pdf

5031490001-PS-000.pdf

5031490002-PS-000.pdf

5031491004-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant

Downloaded from Arrow.com.

Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	503149
Description	CLIK-Mate Plug Housing, 1.50mm Pitch, Dual Row, Positive Lock, 22 Circuits, Natural
Application	Wire-to-Board
Component Type	Housing
Product Name	CLIK-Mate
UPC	884982019560

Agency

UL	E29179

Physical

Downloaded from Arrow.com.

Circuits (maximum)	22
Color - Resin	Natural
Flammability	94HB
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.50mm
Pitch - Termination Interface	1.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.50mm Pitch CLIK-Mate Right-Angle Dual Row PCB Receptacles	213228
1.50mm Pitch CLIK-Mate Right-Angle Dual Row PCB Receptacles	503148
1.50mm Pitch CLIK-Mate Vertical Dual Row PCB Receptacles	213227
1.50mm Pitch CLIK-Mate Right-Angle Dual Row PCB Receptacles	503154

Use with Part(s)

Description	Part Number
Pre-Crimped Lead CLIK-Mate 1.50mm Male-to-CLIK-Mate 1.50mm Male, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black	797581011

Downloaded from Arrow.com.

1.50mm Pitch CLIK-Mate Male Crimp Terminals	502579
1.50mm Pitch CLIK-Mate Male Crimp Terminals	503429
CLIK-Mate 1.50mm Pitch Male Crimp Terminals	213028
CLIK-Mate 1.50mm Pitch Male Crimp Terminals	213029
Pre-Crimped Lead Clik-Mate Male-to-Clik-Mate Male	215710
Pre-Crimped Lead Clik-Mate Male-to-Pigtail	215711

Downloaded from Arrow.com.