

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281
<https://www.phoenixcontact.com/pc/products/1099281>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 PCB connectors, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, material: Metal, connection method: THR reflow/THT wave

Your advantages

- Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- 360° shielding ensures reliable transmission, even in industrial applications
- Housing shield springs enable an optimized EMC shielding concept
- With integrated hybrid LEDs as optical status indicators of data transmission
- Enables data transmission rates of up to 10 Gbps
- Automated handling process thanks to reflow capability
- The extended temperature range from -40°C to +105°C enables use in demanding industrial applications
- Tray packing

Commercial data

Item number	1099281
Packing unit	84 pc
Minimum order quantity	1 pc
Product key	ABNADA
GTIN	4055626947938
Weight per piece (including packing)	5.77 g
Weight per piece (excluding packing)	5.7 g
Customs tariff number	85366930
Country of origin	CN

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

Technical data

Product properties

Product type	Data connector (device side)
Type	RJ45
Number of positions	8
Connection profile	RJ45
Type of packaging	Tray
Housing shield springs	Yes
Number of slots	1
Type	Socket
Shielded	yes
LED	yes

Data management status

Article revision	00
------------------	----

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	72 V DC
Rated surge voltage	1.5 kV DC
Rated surge voltage (III/3)	1.5 kV
Rated surge voltage	1 kV DC
Rated current	1.5 A
Frequency range	10 Hz ... 500 Hz
Insulation resistance	> 500 MΩ
Test voltage	1 kV DC
Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Transmission medium	Copper
Transmission speed	10 Gbps
Power transmission	PoE++

Connection data

Connection technology

Connection method	THR reflow/THT wave
-------------------	---------------------

Dimensions

Width	18 mm
Height	17.6 mm
Length	17.1 mm

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

Installed height	12.80 mm
Orientation to	90.00 °
Data pin length	3.30 mm

Material specifications

Material	Au (1.27 µm/50 µ") (Metal surface contact area (top layer))
	Ni (Metal surface contact area (middle layer))
	Au (Metal surface soldering area (top layer))
	Ni (Metal surface soldering area (middle layer))
	Copper alloy (Housing (shielding))
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	Ni
Contact material	Copper alloy
Contact surface material	Gold

Cable/line

Test voltage Core/Core	1 kV DC
Test voltage Core/Shield	1.50 kV DC
Halogen-free	yes

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 750
Insertion force per signal contact	< 20.00 N
Extraction force per signal contact	< 20 N

Environmental and real-life conditions

Test specification

Frequency	10-500 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm
Acceleration	50.00 m/s ²
Test duration	20.00 s

Test specification

Specification	IEC60068-2-27
Acceleration	295.00 m/s ²

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C

Mounting

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281
<https://www.phoenixcontact.com/pc/products/1099281>

Mounting type	THR soldering
Processing notes	
Moisture Sensitive Level	MSL 2
Classification temperature T _c	260 °C
Solder cycles in the reflow	3

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors




1099281

<https://www.phoenixcontact.com/pc/products/1099281>

Drawings

Diagram



Classification wave soldering profile


CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors




1099281
<https://www.phoenixcontact.com/pc/products/1099281>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1099281>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

cULus Recognized

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281
<https://www.phoenixcontact.com/pc/products/1099281>

Classifications

ECLASS

ECLASS-11.0	27440223
ECLASS-12.0	27440223
ECLASS-13.0	27460201

ETIM

ETIM 9.0	EC002637
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281
<https://www.phoenixcontact.com/pc/products/1099281>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

Accessories

CUC-IND-C1ZNI-S/R4IE10G8 - RJ45 connector

1149846

<https://www.phoenixcontact.com/pc/products/1149846>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: straight, color: yellow, Ethernet

CUC-IND-C1ZNI-S/R4IP10G8 - RJ45 connector

1149847

<https://www.phoenixcontact.com/pc/products/1149847>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 23- 22, cable outlet: straight, color: yellow, Ethernet

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

CUC-IND-C1ZNI-S/R4IP8 - RJ45 connector

1421126

<https://www.phoenixcontact.com/pc/products/1421126>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 23- 22, cable outlet: straight, color: green, Ethernet/PROFINET

CUC-IND-C1ZNI-S/R4IE8 - RJ45 connector

1421607

<https://www.phoenixcontact.com/pc/products/1421607>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: straight, color: green, Ethernet

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

CUC-IND-C1ZNI-S/R4QV6 - RJ45 connector

1406335

<https://www.phoenixcontact.com/pc/products/1406335>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 6, 100 Mbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: straight, High degree of resistance to vibration; 360° shielding; one-piece design; special tool-free assembly, VARAN

CUC-IND-C1ZNI-T/R4IE8 - RJ45 connector

1421877

<https://www.phoenixcontact.com/pc/products/1421877>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: angled, Ethernet

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

CUC-IND-C1ZNI-B/R4IE8 - RJ45 connector

1421876

<https://www.phoenixcontact.com/pc/products/1421876>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: angled, Ethernet

CUC-IND-C1ZNI-B/R4QV6 - RJ45 connector

1406338

<https://www.phoenixcontact.com/pc/products/1406338>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 6, 100 Mbps, CAT5 (IEC 11801:2002), material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: angled, High degree of resistance to vibration; 360° shielding; one-piece design; special tool-free assembly, VARAN

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

CUC-IND-C1ZNI-T/R4QV6 - RJ45 connector

1406341

<https://www.phoenixcontact.com/pc/products/1406341>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 6, 100 Mbps, CAT5 (IEC 11801:2002), material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 26- 24, cable outlet: angled, High degree of resistance to vibration; 360° shielding; one-piece design; special tool-free assembly, VARAN

CUC-IND-C1ZNI-B/R4IP8 - RJ45 connector

1421127

<https://www.phoenixcontact.com/pc/products/1421127>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 23- 22, cable outlet: angled, Ethernet/PROFINET

CUC-IND-J1ST-A/R4LS-LED-PG - RJ45 PCB connectors



1099281

<https://www.phoenixcontact.com/pc/products/1099281>

CUC-IND-C1ZNI-T/R4IP8 - RJ45 connector

1421128

<https://www.phoenixcontact.com/pc/products/1421128>



RJ45 connector, design: RJ45, degree of protection: IP20, number of positions: 8, 1 Gbps, CAT5, material: Metal, connection method: Insulation displacement connection, connection cross section: AWG 23- 22, cable outlet: angled, Ethernet/PROFINET

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG

Flachsmarktstraße 8

D-32825 Blomberg

+49 (0) 5235-3 00

info@phoenixcontact.com