

## har-bus HM Mel. Typ A, AFS 2, Tube




Image is for illustration purposes only. Please refer to product description.

Part number	17 01 154 2201
Specification	har-bus HM Mel. Typ A, AFS 2, Tube
HARTING eCatalogue	<a href="https://harting.com/17011542201">https://harting.com/17011542201</a>

### Identification

Category	Connectors
Series	har-bus <sup>®</sup> HM
Identification	Type A
Element	Male connector
Description of the contact	Straight

### Version

Termination method	Press-in termination
Connection type	Motherboard to daughtercard
Number of contacts	154
Contact configuration	C / A / A / A / A / A / C
Pack contents	Tube

### Technical characteristics

Contact rows	7
Contact spacing (termination side)	2 mm
Contact spacing (mating side)	2 mm
Rated current	1 A
Data rate	≤2,500 Mbit/s
Insulation resistance	>10 <sup>9</sup> Ω
Contact resistance	≤20 mΩ
Limiting temperature	-55 ... +125 °C
Insertion force	≤115.5 N

Page 1 / 3 | Creation date 2026-02-11 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97200 | [electronics@HARTING.com](mailto:electronics@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)



Pushing Performance  
Since 1945

## Technical characteristics

Withdrawal force	≥23.1 N
Performance level	2
Test voltage $U_{r.m.s.}$	0.75 kV
Isolation group	IIIa ( $175 \leq CTI < 400$ )
PCB thickness	≥1.4 mm

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled
Colour (insert)	Beige
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
----------	--

## Commercial data

Packaging size	10
Net weight	7.522 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140120143
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637



**Pushing Performance**  
Since 1945

## Commercial data

UNSPSC 24.0

39121415

---