





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING

924CE1-T3




NOTES

- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
- 2 - THE MINIMUM PLUNGER TRAVEL PAST BREAK, FOR A SAFE CONTACT GAP IS .060
- 3 - MAKE BEFORE BREAK CIRCUITRY

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS		ELECTRICAL DATA		SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 5.1 LB MAX		CONTACT ARRANGEMENT S P D T D B		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT		
OVERTRAVEL — — — — .020 MIN		10A-250 VAC 1/3HP-125 OR 250 VAC 				

924CE1-T3

M

DRAWING
NUMBER

2

ISSUE

REPLACES
RELEASE NO. PR-14729

CHECK

REVISIONS

A CO-69061
S A V 29 AUG 91

CHECK

DDM/CAD

DRAWN

CHECK

S A V 29 AUG 91