
UDK-RELG 7 - Basic terminal block

2777069

https://www.phoenixcontact.com/ae/products/2777069

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Basic terminal blocks with test pick-off on both sides and double connections with the same potential for NS 32 and NS 35/7,5 DIN rail, with end cover, for ST-REL..., ST-OV..., and ST-OE... plugs, 7-pos.

Commercial data

Item number	2777069
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	DK6
Product key	DK61B4
GTIN	4017918068653
Weight per piece (including packing)	111.27 g
Weight per piece (excluding packing)	102.506 g
Customs tariff number	85366990
Country of origin	TR

Downloaded from Arrow.com.

Technical data

Product properties

Product type	Relay socket
Number of positions	7


Electrical properties

Nominal voltage U_N	400 V (voltage is determined by the coupling connector.)
Nominal current I_N	16 A (current is determined by the coupling connector.)

Connection data

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm² ... 4 mm²
Conductor cross-section flexible	0.2 mm² ... 4 mm²
Conductor cross-section AWG	24 ... 12

Dimensions

Dimensional drawing	
Width	45.6 mm (with cover)
Height	63.6 mm
Depth	113 mm

Material specifications

Color	gray (RAL 7042)
Insulating material	PA

Environmental and real-life conditions


Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Downloaded from Arrow.com.


Drawings

Dimensional drawing



Downloaded from Arrow.com.


Schematic diagram



1-3 = fixed bridge, cross connection rail, spacer

Downloaded from Arrow.com.

Schematic diagram



1 = Coupling connector
2 = Coding
3 = Cover
4 = Basic termination block

Downloaded from Arrow.com.

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/ae/products/2777069

cUL Recognized
Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	15 A	30 - 12	-

UL Recognized
Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	300 V	15 A	30 - 12	-

Downloaded from Arrow.com.

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 9.0	EC001456

UNSPSC

UNSPSC 21.0	39122300

Downloaded from Arrow.com.

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8e8415dd-062a-424c-9b9a-2fadb40d8f67

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Middle East FZ LLC
1201N-1206N, Dubai Science Park Towers – North
P.O. Box 345002, Dubai, United Arab Emirates
(+971) 4 437-0324
info-me@phoenixcontact.com

Downloaded from Arrow.com.