





Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.



RECOMMENDED PCB LAYOUT



Technical data

- 1.Nominal voltage: 300V/15A
PITCH:5.0mm
- 2.Insulation Withstanding Voltage:
AC 1600V/MIN
- 3.Insulation Resistance:
1000MΩ or more at DC500V
- 4.Operating temperature range:-40°C ~115°C
- 5.Soldering temperature range:250°C±10°C/5sec
- 6.Safety approval:
- 7.RoHS Compliance
- 8.Undimensioned Tolerances:

Dim.L=Px5.0+2.0 Dim.B=(P-1)x5.0 P= number of poles 2-24P		
0-30mm	Dim B ±0.15	Dim L ±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

Part No.:

OSTOQXX7150

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	2: Red
...	3: Orange
24 24 Poles	4: Yellow
	5: Green (Standard)
	6: Blue
	8: Grey
Nonstandard colors Mins could apply	

2	PIN	BRASS	TIN PLATED	P
1	BODY	PA66 UL94V-0		1
ITEM	NAME OF PART	MATERIAL	NOTES	Q"TY
DWG.	Marvin Zhang	DATE 2016.05.21	UNITS: MM	SHEET: 1 OF 1
CHK.	Marvin Zhang	DATE 2016.05.21	SCALE: NONE 3:1 (:)	REV.: A
APP.		DATE	TITLE: OSTOQ 5.0 Series	X. ±0.50
			Close type Vertical (180D)	X.X ±0.30
			PART NO. OSTOQXX7150	X.XX ±0.10
			DWG NO. OSTOQXX7150.dwg	X* ±1°
ON-SHORE TECHNOLOGY, INC.				

△	DESCRIPTION	CHK.	DATE
SIGN			