



**Part Number :** [732520092](#)

**Product Description :** Precision Test Connector, 2.92mm PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, without Screws, 50 Ohms

**Series Number :** 73252

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents and Resources


### Drawings

[732520092\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	RF / Coaxial Connectors
Series	73252
Description	Precision Test Connector, 2.92mm PCB Jack Receptacle, 2-Hole Flange Mount, Solderless Compression Contact, without Screws, 50 Ohms
Application	RF
Comments	Solderless Compression
Product Name	Precision Test - 2.92mm
Style	PCB
Type	Subminiature
UPC	884982956001

#### Electrical

Frequency	40 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

#### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.848/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A

PCB Mounting	Surface Mount - Compression
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

This document was generated on Dec 17, 2025