



Pushing Performance  
Since 1945

# PCB r. hous. & insert back M. 1pc w/o FE



Image is for illustration purposes only. Please refer to product description.

Part number	21 03 396 1533
Specification	PCB r. hous. & insert back M. 1pc w/o FE
HARTING eCatalogue	<a href="https://harting.com/21033961533">https://harting.com/21033961533</a>

## Identification

Category	Connectors
Series	Circular connectors M12
Identification	Power
Element	PCB adapter
Specification	Straight incl. housing for rear mounting

## Version

Termination method	Reflow soldering termination (THR)
Gender	Male
Shielding	Shielded
Number of contacts	4
Coding	L-coding
Locking type	Screw locking

## Technical characteristics

Rated current	16 A
Rated voltage	63 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Overvoltage category	III
Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$



**Pushing Performance**  
Since 1945

## Technical characteristics

Tightening torque	2 Nm Lock nut
Limiting temperature	-40 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Isolation group	I (600 ≤ CTI)

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Au over Ni Mating side
Material (hood/housing)	Zinc die-cast
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 61076-2-111
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

## Commercial data

Packaging size	1
Net weight	28.333 g
Country of origin	Romania



Pushing Performance  
Since 1945

Commercial data

European customs tariff number	85366990
GTIN	5713140228443
eCl@ss	27460201 PCB connector (board connector)
ETIM	EC002637
UNSPSC 24.0	39121415