

HONEYWELL PART NUMBER
11SM701
PRODUCT CODE TWY1900

REV	DOCUMENT	CHANGED BY	CHECK
6	0038442	SSK 31MAR08	BLR


B

A

A

B

A



NOTE—
▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .087 MAX DIA ON .375±.002 CENTERS
2-TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.	PR - 2130
REPLACES	-

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH			DRAWN	VK	06 FEB 08	Honeywell						
OPERATING FORCE — — 56 GRAM MAX	CONTACT ARRANGEMENT SPDT			TOLERANCES UNLESS NOTED:			CHECK	RJ	06 FEB 08							
RELEASE FORCE— — — — 14 GRAM MIN	30 VOLTS DC RATING			NO PLACE X ±			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC						
DIFFERENTIAL TRAVEL— — — .002 MAX			SEA LEVEL	50,000 FT		0.030										
	INDUCTIVE	3 AMP	2.5 AMP		0.015											
	RESISTIVE	5 AMP	5 AMP		0.005											
OVERTRAVEL — — — — — .005 MIN	MAXIMUM INRUSH 24 AMP			FOUR PLACE .XXXX ±			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV		
APPROVALS				THIRD ANGLE PROJECTION						B	I	11SM701		6		
	UL, CSA	4A, 250 VAC	UL	CS	BRAND	L119	RASTER			SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1			