



Product: [5302F1](#) 

Security & Sound, #18-4c, TC, Shielded, CMG-FPL-PLTC-ER, Water-Blocked

Product Description

Security & Sound Cable, Rated-CMG-FPL-PLTC-ER, 4-18 AWG stranded tinned copper conductors with PVC insulation, waterblocking tape, Beldfoil® shield and PVC jacket

Technical Specifications

Product Overview

Suitable Applications:	Security System, Intercom/PA, Audio/Speaker, Power-Limited Controls, Noisy & Wet Location, Below-Grade Duct
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	18	7x26	TC - Tinned Copper	4

Conductor Count:	4
------------------	---

Insulation

Element	Material	Nominal Wall Thickness
Conductor(s)	PVC - Polyvinyl Chloride	0.010 in

Color Chart

Number	Color
1	Black
2	White
3	Red
4	Green

Outer Shield Material

Material	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Alum / Poly	100 %	TC - Tinned Copper	20	7x28

Outer Jacket Material

Material	Nominal Diameter	Separator Material
PVC - Polyvinyl Chloride	0.259 in	Waterblocking Tape

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR
6.6 Ohm/1000ft	6.6 Ohm/1000ft		15.25 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor
40 pF/ft

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	105°C
Operating Temp Range:	-30°C To +105°C

Mechanical Characteristics

Bulk Cable Weight:	42 lbs/1000ft
Max Recommended Pulling Tension:	102 lbs
Min Bend Radius/Minor Axis:	2.75 in

Standards

NEC Articles:	800, 760, 725
NEC/(UL) Specification:	CMG, FPL, PLTC, PLTC-ER
CEC/C(UL) Specification:	CMG

Applicable Environmental and Other Programs

Environmental Space:	Water Exposure/Below-Grade Conduit
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-11-06
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 (FT4 Loading)
CSA Flammability:	FT4
IEEE Flammability:	IEEE 1202
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
5302F1 0101000	Black	Reel	1,000 ft	612825159599
5302F1 0021000	Red	Reel	1,000 ft	612825159582

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.222 Revision Date: 05-11-2020
----------------------	--

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.