

Multilayer Ceramic Chip Capacitors

Product Top Page

Search by Part No.

Search by Characteristics

Cross Reference

Catalog

Tech Notes

Technical Support Tools

FAQ

CGA4C4NP02W221J060AA

?



TDK item description ? CGA4C4NP02W221JT****

Applications



Automotive Grade

Feature

Mid

Mid Voltage (100 to 630V)

150°C

High Temperature Application

AEC-Q200

AEC-Q200


Series

CGA4(2012) [EIA 0805]

Status



Production



Images are for reference only and show exemplary products.

PDF file of this page



Buy Now



Contact



Documents

Catalog

Specification

RoHS Certificate

SVHC/REACH Certificate

Characterization Sheet

Promotion Video

Sample Kits

Size

Length(L) 2.00mm ±0.20mm

Width(W) 1.25mm ±0.20mm

Thickness(T) 0.60mm ±0.15mm

Terminal Width(B) 0.20mm Min.

Terminal Spacing(G)

Recommended Land Pattern (PA) 1.00mm to 1.30mm(Flow Soldering)
0.90mm to 1.20mm(Reflow Soldering)

Recommended Land Pattern (PB) 1.00mm to 1.20mm(Flow Soldering)
0.70mm to 0.90mm(Reflow Soldering)

Recommended Land Pattern (PC) 0.80mm to 1.10mm(Flow Soldering)
0.90mm to 1.20mm(Reflow Soldering)

Electrical Characteristics

Capacitance 220pF ±5%

Rated Voltage 450VDC

Temperature Characteristic ? NP0(0±30ppm/°C)

Q (Min.) 1000

Insulation Resistance (Min.) 10000MΩ

Other

Soldering Method Wave (Flow)
Reflow


AEC-Q200 Yes

Packing Punched (Paper)Taping [180mm Reel]


Package Quantity 4000pcs







Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)

Impedance



ESR





Products

» Search by Part No. » Search by Characteristics » Distributor Inventory Check

- » Capacitors
- » Inductors (Coils)
- » EMC Components
- » RF Components and Modules
- » Voltage / Current / Temperature Protection Devices
- » Sensors and Sensor Systems
- » Ceramic Switching / Heating, Piezo Components, Buzzers and Microphones
- » Transformers
- » Ferrites and Accessories
- » Noise Suppressing / Magnetic Sheet
- » Anechoic Chambers and Radio Wave Absorbers
- » Power Supplies
- » Magnets
- » Flash Storages
- » Wireless Power Transfer
- » FA Systems
- » Transparent Conductive Film
- » Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB)
- » Solar Cells
- » Biosensor

Application Guides

Technical Support

Tech Library

Environment

Contact

News

Home

- About TDK
- TDK Worldwide

