

30mA, 40V Schottky Barrier Diode

FEATURES

- Low reverse current
- Surface mount device type
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Adapters
- For switching power supply
- Low stored charge
- Inverter

MECHANICAL DATA

- Case: SOD-523F
- Molding compound meets UL 94 V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 1A whisker test
- Polarity: Indicated by cathode band
- Weight: 1.60 mg (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	30	mA
V_{RRM}	40	V
V_F at $I_F = 1\text{mA}$	0.37	V
$T_{J\text{ MAX}}$	125	°C
Package	SOD-523F	
Configuration	Single die	



SOD-523F



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	RB751M5-40	UNIT
Marking code on the device		5	
Repetitive peak reverse voltage	V_{RRM}	40	V
DC block voltage	V_R	30	V
Forward current	I_F	30	mA
Non-repetitive peak forward surge current @ $t = 8.3\text{ms}$	I_{FSM}	0.2	A
Power dissipation	P_D	200	mW
Junction temperature range	T_J	-55 to +125	°C
Storage temperature range	T_{STG}	-55 to +125	°C

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage ⁽¹⁾	$I_F = 1\text{mA}$, $T_J = 25^\circ\text{C}$	V_F	-	0.37	V
Reverse current ⁽²⁾	$V_R = 30\text{V}$, $T_J = 25^\circ\text{C}$	I_R	-	0.50	μA
Capacitance	$V_R = 1\text{V}$, $f = 1\text{MHz}$	C	2	-	pF

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE	PACKAGE	PACKING
RB751M5-40 RSG	SOD-523F	8K / 7" Reel

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Typical Forward Characteristics




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Capacitance Characteristics







Fig.4 Power Derating Curve




PACKAGE OUTLINE DIMENSION

SOD-523F



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	0.50	0.77	0.020	0.030
b	0.25	0.40	0.010	0.016
c	0.07	0.20	0.003	0.008
D	1.10	1.30	0.043	0.051
E	0.70	0.90	0.028	0.035
H	1.50	1.70	0.059	0.067

SUGGEST PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	0.80	0.031
B	0.60	0.024
C	2.30	0.091

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.