


ELFB SERIES PART NUMBERING SCHEME

REV	ECN	APP'D
-	4501	10 10-31-01
A	5742	2N12/28/05



COLOR/ PLATING
 0=BLACK, TIN (STANDARD)
 1=BLACK, SELECTIVE GOLD
 G=GREEN, TIN
 1G=GREEN, SEL. GOLD


CONSULT PCD FOR PART NO. AND
 AVAILABILITY OF FOLLOWING OPTIONS:
 *CUSTOM COLORS *CUSTOM KEYING
 *CUSTOM MARKING *NUMBER OF POSITIONS 21-24

MATERIALS:
 HOUSING: NYLON 46, UL 94 V-0; HIGH TEMP.
 CONTACT: PHOSPHOR BRONZE, TIN FINISH

MAX OPERATING TEMP: 125°C

NOTE:
 HIGH TEMP. MATERIAL WILL WITHSTAND COMPONENT
 EQUILIBRIUM TEMPERATURES OF 260°C FOR
 3 MINUTES DURING THE SOLDERING PROCESS

PRINTED CIRCUIT BOARD CONFIGURATION



RECOMMENDED PCB THICKNESS: .062±.008

DIMENSIONS

ANSI Y14.5M
 UNITS: INCHES
 Pro/E FILE

TOLERANCES

.XX ±0.01
 .XXX ±0.005
 ANGLES ±2.0°

PROJECTION



Amphenol Pcd

ENGR

C. LASHUA 5/21/01

CHKD

ALAN PATRIE 10-30-01

APPD

10 10-31-01

TITLE

ELFB SERIES
 INVERTED HEADER

ORIGINAL
 STAMPED
 IN RED

THIS DOCUMENT CONTAINS
 PROPRIETARY INFORMATION WHICH
 IS THE CONFIDENTIAL PROPERTY
 OF AMPHENOL PCD, INC.
 PEABODY, MA, USA

SIZE

A

DWG NO.

ELFB02230

REV

A



CODE: 58982

SCALE: NONE

SHEET 1 OF 2



RIGHT ANGLE

L=NUM OF POS X .200



VERTICAL

L=NUM OF POS X .200



SIZE
A

DWG NO.

ELFB02230

REV
A

CODE: 58982

SCALE: NONE

SHEET 2 OF 2