
**Part Number :** 1511200014
**Product Description :** 2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Right-Angle, Surface Mount, 2.00µm Tin (Sn) Plating, 14 Circuits, Glow-Wire Capable, Tape and Reel
**Series Number :** 151120
**Status :** Active
**Product Category :** PCB Headers and Receptacles



## Documents and Resources

### Drawings

1511200014_sd.pdf

PK-151120-3000-001.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

503940001-AS-000.pdf

503940002-AS-000.pdf

PS-151117-0001-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 151120 |
| Description | 2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Right-Angle, Surface Mount, 2.00µm Tin (Sn) Plating, 14 Circuits, Glow-Wire Capable, Tape and Reel |
| Application | Board-to-Board, Wire-to-Board |
| Component Type | PCB Header |
| Product Name | Milli-Grid |
| UPC | 889056761567 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 2.0A |
| Voltage - Maximum | 125V AC |

### Physical

Downloaded from Arrow.com.

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 14 |
| Circuits (maximum) | 14 |
| Color - Resin | Black |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Gender | Male |
| Glow-Wire Capable | Yes |
| Guide to Mating Part | No |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Liquid Crystal Polymer (LCP) |
| Net Weight | 0.822/g |
| Number of Rows | 2 |
| Orientation | Right Angle |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Retention | No |
| Pitch - Mating Interface | 2.00mm |
| Pitch - Termination Interface | 2.00mm |
| Plating min - Mating | 2.000µm |
| Plating min - Termination | 2.000µm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Shrouded | Shrouded |
| Stackable | No |
| Temperature Range - Operating | -55° to +105°C |
| Termination Interface Style | Surface Mount |

**Solder Process Data**

| | |
|---|---|
| Max-Duration | 11 |
| Lead-Free Process Capability | SMC&WAVE |

Downloaded from Arrow.com.

| | |
|---|---|
| Max-Cycle | 1 |
| Max-Temp | 265 |

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| Milli-Grid Dual Row Receptacle Housings | 151192 |
| Milli-Grid Dual Row Receptacle Housings | 51110 |
| Milli-Grid Vertical Through Hole PCB Receptacles | 78787 |
| Milli-Grid Top Entry Surface Mount PCB Receptacles | 78788 |
| Milli-Grid Vertical Through Hole PCB Receptacles | 79107 |
| Milli-Grid Top/Bottom Entry Surface Mount PCB Receptacles | 79109 |



Downloaded from Arrow.com.