


Connectors > Rectangular Connectors > Rectangular Contact Inserts

5-1195085-3 ACTIVE

Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 10 Position, Sealable, 20 – 26 AWG Wire Size, .5 – .14 mm² Wire Size, 1.5 A



RAYCHEM

TE Internal #: **643679-000**
TE Internal Description: **MTC100-YA1-009**

Rectangular Connector Insert Type : **Contact Insert**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **10**
Centerline (Pitch) : **1.27 mm [.05 in]**

Add to List ▾ | [Similar Products](#) | [Digital Datasheet](#)

[Compatible Parts & Tooling](#)

Documents	Features	Product Compliance
Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.		
Product Type Features	Rectangular Connector Insert Type : Contact Insert Connector System : Wire-to-Wire Sealable : Yes Connector & Contact Terminates To : Wire & Cable	
Configuration Features	Number of Positions : 10	
Body Features	Primary Product Color : Black Primary Product Material : High Grade Polyarylene Thermoplastic Seal Type : Interfacial Seal	
Contact Features	Contact Type : Socket Contact Current Rating (Max) (A): 1.5	
Mechanical Attachment	Polarization Code : A2 Connector Mounting Type : Panel Mount	
Housing Features	Centerline (Pitch) : 1.27 mm [.05 in]	
Dimensions	Wire Size (AWG): 20 – 26 Wire Size (mm²): .5 – .14	
Usage Conditions	Operating Temperature Range : -65 – 125 °C [-85 – 257 °F]	
Operation/Application	Compatible With Connector Shell Size : 50.8 [2.0]	

Compatible Parts

There are no compatible parts for this product.
Please reach out to Product Support to help with your request.

[>Contact Product Support](#)

Products with Similar Specs

[View All Similar Products](#)

THIS PRODUCT

RECTANGULAR CONTACT INSERTS
5-1195085-3
Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 10...

Non-Stocked

Rectangular Connector Insert Type : **Contact Insert**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **10**
Centerline (Pitch) : **1.27 mm**

TOP RESULTS ?

RECTANGULAR CONTACT INSERTS
1-1196701-4
Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 10...

Non-Stocked

Rectangular Connector Insert Type : **Contact Insert**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **10**
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS
697123-000
Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 20...

In-Stock

Rectangular Connector Insert Type : **Contact Insert**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **20**
Centerline (Pitch) : **1.27 mm**

RECTANGULAR CONTACT INSERTS
697121-000
Rectangular Contact Inserts, Contact Insert, Socket, Wire-to-Wire, 20...

In-Stock

Rectangular Connector Insert Type : **Contact Insert**
Contact Type : **Socket**
Connector System : **Wire-to-Wire**
Number of Positions : **20**
Centerline (Pitch) : **1.27 mm**

Customers Also Bought

TE Part #: **MTC100-KT2-0079**

Standard Rectangular Connectors, Housing Kit...

[View Product](#)

TE Part #: **D-EASY 03 B 03**

Feedthroughs, Thread Length .079 in [2 mm]...

[View Product](#)

Contact Our Team – 24/7 Support
 +1 800 522 6752
 Live Chat
[See Support Details](#)
Connect With Us

Access Partner Information
[Distributors](#)
[Suppliers](#)
[Supplier Diversity](#)

Get Answers Now
[Authorized Distributors & Resellers](#)
[Product FAQs](#)
[Samples FAQs](#)
[TE Store FAQs](#)
[Terms and Conditions of Sale](#)
[Samples Terms and Conditions](#)

Select Your Preferences
Language
English (EN)
Ship to
 United States (\$USD)

TE Connectivity empowers engineers by designing and manufacturing sensor and connectivity solutions for our increasingly connected world.

[Terms of Use](#) | [Privacy](#) | [US Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Security](#) | [Site Map](#) | © 2024 TE Connectivity. All Rights Reserved.

Downloaded from [Arrow.com](#)

Feedback