

# G-INS-M63-L68L-PNES-BK - Cable gland



1411139

<https://www.phoenixcontact.com/us/products/1411139>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland, material for screw connection: PA, application: Standard, external cable diameter 34 mm ... 44 mm, shielding: no, connecting thread: M63 x 1.5, color: jet black RAL 9005

## Your advantages

- Plastic material conforms to UL 746C f1

## Commercial data

Item number	1411139
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF68
Product key	AF7DCX
Catalog page	Page 686 (C-2-2019)
GTIN	4046356922715
Weight per piece (including packing)	106.4 g
Weight per piece (excluding packing)	106.4 g
Customs tariff number	39269097
Country of origin	TR

# G-INS-M63-L68L-PNES-BK - Cable gland



1411139

<https://www.phoenixcontact.com/us/products/1411139>

## Technical data

### Mounting

Assembly note	1) Mount screw connection support in the housing using the correct torque 2) Insert cable 3) Tighten union nut using the correct torque
---------------	---


### Product properties

Product type	Cable screw gland
Application	Standard
No. of conductors	1
Manufacturer	BIMED
Manufacturer Designation	BM-30
Shielded	no
Execution of the strain relief	A

### Characteristics

Category of shock impact	4
Design, Strain relief	A

### Dimensions

Dimensional drawing	
Length	75 mm
Length of the connecting thread	18 mm
Hole diameter	63.1 mm ... 63.3 mm
Wrench size, union nut	65 mm
Wrench size, support	65 mm
Hexagon angular dimension	72.2 mm
Thread type connection side	M63 x 1.5
Thread pitch	1.5 mm

### Connection data

Tightening torque	20 Nm (Cap nut)
	12 Nm (Support: EN 62444)
	20 Nm (for UL514 B: union nut)

### Material specifications

Color	black (RAL 9005)
Material Housing	PA (Housing)
Flammability rating according to UL 94	V2

# G-INS-M63-L68L-PNES-BK - Cable gland



1411139  
<https://www.phoenixcontact.com/us/products/1411139>

Seal material Cable seal	CR
Material for screw connection	PA

## Cable/line

External cable diameter Cable 1	34 mm ... 44 mm
External cable diameter	34 mm ... 44 mm (for UL 514 B)
Halogen-free	no

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66
	IP68 (5 bar / 0.5 h)
Enclosure rating (NEMA)	1
	4
	4X
	12
	13
Ambient temperature (operation)	-40 °C ... 100 °C (static)

# G-INS-M63-L68L-PNES-BK - Cable gland


1411139

<https://www.phoenixcontact.com/us/products/1411139>



## Drawings

Dimensional drawing



Dimensional drawing

# G-INS-M63-L68L-PNES-BK - Cable gland



1411139

<https://www.phoenixcontact.com/us/products/1411139>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411139>



**CSA**

Approval ID: 115116



**VDE approval of drawings**

Approval ID: 40024418



**UL Listed**

Approval ID: E199260



**cUL Listed**

Approval ID: E199260

# G-INS-M63-L68L-PNES-BK - Cable gland



1411139

<https://www.phoenixcontact.com/us/products/1411139>

## Classifications

### ECLASS

ECLASS-13.0	27140801
-------------	----------

### ETIM

ETIM 9.0	EC000441
----------	----------

### UNSPSC

UNSPSC 21.0	39121300
-------------	----------

# G-INS-M63-L68L-PNES-BK - Cable gland



1411139

<https://www.phoenixcontact.com/us/products/1411139>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)