



PANEL MOUNTING



CONTACT ARRANGEMENT

code for x	function	toggle towards keyway	toggle opposite to keyway
D	On-On	1-2	2-3

code for x	function	toggle towards keyway	toggle in center	toggle opposite to keyway
E	On-Off-On	1-2	open	2-3

Compliance: RohS III (2015/863/EU)

Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date 08/09	Name dr
Accessory	02/25	dr		
Revised	10/17	dr	knitter-switch	
Dimension	01/11	dr		
Panel mouting	05/10	dr		
Modifications	Date	Name		

MTL 106 x

30 19 07


Page 1/2

Downloaded from Arrow.com.


Specifications:

Contact rating:	3A, 250V AC / 6A, 125V AC 4A, 30V DC / 5A, 12V DC 6A, 6V DC
Contact resistance:	20mOhm max.
Insulation resistance:	1 000MOhm min. at 500V DC
Dielectric strength:	1 500V, 50Hz for the duration of 1 minute
Operating temperature:	-45°C to +140°C
Mechanical life:	min. 200 000 cycles
Soldering conditions:	hand-soldering: max.: 420°C, 3sec., 60W auto-soldering: max.: 270°C, 5sec.
Mounting instruction:	max. torque: 49Ncm
Material:	Terminal: brass, C1020 silver plated Case: DAP Housing: stainless steel, CNS9265 Bushing: copper alloy, C3604BD nickel plated Actuator: copper alloy, C3604BD chrome plated Cap: aluminium, (not included)
Accessory:	(included)


TOOTH WASHER, T 1440-1M03
Material: SUS 304



LOCK WASHER, L 675-1M05
Material: SPCC, nickel plated



NUT, H 675-1M41
Material: C3604, nickel plated



Compliance: RohS III (2015/863/EU)

Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm			Date 08/09	Name dr	MTL 106 x
Accessory	02/25	dr			
Revised	10/17	dr	knitter-switch		30 19 07
Dimension	01/11	dr			Page 2/2
Panel mouting	05/10	dr			
Modifications	Date	Name			

Downloaded from Arrow.com.