



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL DRAWING (EAR 13920)	JUL28/11	S.M








END VIEW IN MATED CONDITION
(MATED TO P/N LCC17-A3W3SM-4N1)





LOCATE HOLES
⌖ 0.13[.005] DIA
POSITION DIMENSIONS
ARE BASIC

NOTE:

1) MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT
PER EU DIRECTIVE 2002/95/EC AND AMENDMENTS.
- SHELLS - STAMPED STEEL, TIN OVER NICKEL PLATED
- INSULATOR - ENGINEERING THERMOPLASTIC, GLASS REINFORCED, HIGH TEMPERATURE RESISTANT, UL FLAMMABILITY RATING 94V-0, BLACK
- CONTACTS - COPPER ALLOY, PLATED WITH NICKEL FOLLOWED BY 30 µ" [0.76 µm] GOLD ON THE MATING AREA AND GOLD ON THE TAILS
- BOARDLOCK - COPPER ALLOY, TIN PLATED

2) ELECTRICAL CHARACTERISTICS

- CURRENT RATING: 55 A PER CONTACT
- CONTACT RESISTANCE: 5 MILLIOHMS MAX
- OPERATING TEMPERATURE: -40 °C TO +105 °C

PART NUMBER: LCC17-A3W3PE-AN1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS SPECIFIED OTHERWISE	DRAWN	S.CAELERS	JUL28/11
PRIMARY UNITS INCHES	CHECKED	S.MUGAN	JUL28/11
SECONDARY MILLIMETERS	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.	EAR 13920	
2 DECIMAL PLACES	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	
ANGULAR DEGREES			

Amphenol Canada Corp.

LCC17 COOLPOWER D-SUB CONNECTOR, 3W3 ARRANGEMENT, PIN PCB TAIL POWER , #4-40 THREAD, BOARDLOCK, CONTACTS IN A1 & A3 ONLY, RoHS COMPLIANT

DWG. NO.	REV
P-LCC17-A3W3PE-AN1	A

CODE ID NO.	DWG SIZE:	SCALE:	SHEET
03554	C	4:1	1 OF 1

Downloaded from Arrow.com.