




REV. 1
DCO 16356


COIL: @ 25°C
 RESISTANCE $540 - 770 \text{ OHMS}$
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 13.0 VDC
 MUST RELEASE $10.1 \text{ VDC MAX., } 2.3 \text{ VDC MIN.}$

ENVIRONMENT:

VIBRATION $10 \text{ CPS TO } 2000 \text{ CPS @ } 15 \text{ g's}$
 SHOCK $100 \text{ g's } 6 \pm 1 \text{ MS. DURATION}$
 TEMPERATURE $-65^{\circ}\text{C TO } +125^{\circ}\text{C}$

NOTES: OPERATE & RELEASE 6 MS MAX.
 CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: $2\text{A } 28 \text{ VDC RESISTIVE } 100,000 \text{ OPERATIONS MINIMUM}$

DR. PBB 5-5-00

CK. TLG 7-12-00

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M5757/10-054 REV.

"FW" RELAY

FW1201G0B