



Part Number : [1720503064](#)

Product Description : EdgeLine+ ESP Vertical Connector, 15 Gbps, 0.75mm Pitch, 1.57mm PCB Thickness, 40.0A Power Module, 64 Circuits, 2 Power Circuits

Series Number : 172050

Status : Active

Product Category : Card Edge Connectors



Documents and Resources

Drawings

[1720503064 sd.pdf](#)

[PK-172052-1000-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-172050-3064-001.zip](#)

[1720500004-000.pdf](#)

[1720500004-000.zip](#)


Specifications

[AS-172050-0001-001.pdf](#)

[PS-172050-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Card Edge Connectors
Series	172050
Description	EdgeLine+ ESP Vertical Connector, 15 Gbps, 0.75mm Pitch, 1.57mm PCB Thickness, 40.0A Power Module, 64 Circuits, 2 Power Circuits
Component Type	Edgecard to PCB
Product Name	EdgeLine
UPC	887191487137

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.5A, 40.0A
Data Rate	12.5-20.0 Gbps

High Power Bay (30.0A or more)	Yes
Voltage - Maximum	250V AC (RMS)/DC

Physical

Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Black
Durability (mating cycles max)	200
Edge Card Thickness	1.57mm
Entry Angle	N/A
Flammability	94V-0
Keying to Mating Part	N/A
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.215/g
Orientation	Vertical
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.79mm
Pitch - Mating Interface	0.75mm
Pitch - Termination Interface	0.75mm
Plating min - Mating	0.762μm
Plating min - Termination	0.762μm
Polarized to Mating Part	Yes
(p)ower-(s)ignal Configuration	64s - 0p
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2

Max-Temp	260
----------	-----

This document was generated on Apr 14, 2026