

CGA9M1X7T2J334M200KC

TDK Item Description : CGA9M1X7T2J334MT****



Equivalent C5750X7T2J334M for Automotive

Application & Main Feature

Automotive Grade (Mid Voltage (100 to 630V))

Series

CGA9(5750) [EIA CC2220]

Dimensions

L 5.70mm +/-0.4mm
W 5.00mm +/-0.4mm
T 2.00mm +/-0.2mm
B 0.20mm Min.
G

Temperature Characteristic

X7T (-55 to 125 degC +22,-33%)

Rated Voltage

2J (630Vdc)

Capacitance

330nF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor


2.5% Max.

Insulation Resistance


1.52Gohm Min.

AEC-Q200


Yes




DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 4, 2016