

**Part Number :** [936000026](#)

**Product Description :** Heavy-Duty Metal Cable Gland - 5 Bar, for 11.00-18.00mm Cable, M25x1.5 Thread

**Series Number :** 93600

**Status :** Active

**Product Category :** Heavy-Duty Cable Glands

**Engineering Part Number :** 7000.6832.0



---

## Documents and Resources

### Drawings

[936000026 sd.pdf](#)

[STEP AP242](#)


[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Cable Glands
Series	93600
Description	Heavy-Duty Metal Cable Gland - 5 Bar, for 11.00-18.00mm Cable, M25x1.5 Thread
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Product Name	Heavy-Duty Connectors
UPC	887191822587

### Physical

Cable Diameter	11.00-18.00mm
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	58.000/g
Packaging Type	Bag
Panel Cutout Diameter	25.50mm
Temperature Range - Operating	-40° to +125°C
Thread Size	M25x1.5
Thread Type	(M) Metric
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Use With	Industrial connector hoods and housings

---

This document was generated on Jun 09, 2026