
SK3984

POSITRONIC INDUSTRIES BELIEVES THE DATA ON THIS DRAWING TO BE RELIABLE, SINCE THE TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE, THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC INDUSTRIES ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.

| DATE | REV | REVISION RECORD | APP | DR | CK |
|---|---|---|---|---|---|
| 10-19-01 | NC | ECO 18477 | | YK | |
| | | | | | |
| | | | | | |
| | | | | | |




NOTES:
1. MATERIALS AND FINISHES:
   INSULATOR - GLASS FILLED DAP PER ASTM-D-5948 TYPE SDG-F, COLOR GREY.
   CONTACTS - COPPER ALLOY, 0.000015 (0.38µ) GOLD OVER COPPER PLATE.
   JACKSCREWS - STAINLESS STEEL, PASSIVATED.
   HEX NUTS AND LOCK WASHERS - STAINLESS STEEL, PASSIVATED.
2. ELECTRICAL CHARACTERISTICS:
   CONTACT CURRENT RATING - 5 AMPS MAXIMUM.
   INITIAL CONTACT RESISTANCE - 0.012 OHMS MAXIMUM.
   INSULATION RESISTANCE - 5G OHMS MINIMUM.
   WORKING TEMPERATURE - -55°C TO +135°C.
3. DIMENSIONS ARE IN INCHES (MILLIMETERS).

POSITRONIC INDUSTRIES INC.
www.connectpositronic.com

| | | | |
|---|---|---|---|
| DECIMAL TOL. ±0.015 [0.38] | SGM SERIES | SCALE N.T.S. | DRAWN BY Y. KELLEYBREW |
| WF # 4087 | TITLE SGM7MDS4T0000 | | APPROVED BY |
| ANGULAR TOL. ±5° | DATE 10-19-01 | DRAWING NUMBER SK3984 | REV. NC |

Downloaded from Arrow.com.