




Part Number : [764505107](#)
Product Description : Impact 100 Ohm 2 Pair Right-Angle Male Header, Right Guided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free
Series Number : 76450
Status : Active
Product Category : Backplane Connectors



Documents & Resources

Drawings
[764505107_sd.pdf](#)
[PK-70873-077-001.pdf](#)

3D Models and Design Files
[764505107_stp.zip](#)
[EE-76450-002-001.pdf](#)
[EE-76450-50G-001.pdf](#)
[SP-76450-002-001.zip](#)
[SP-76450-50G-001.zip](#)
[SYM-76450-5107-001.zip](#)

Specifications
[AS-76060-990-001.pdf](#)
[AS-76060-9999-001.pdf](#)
[PS-45499-002-001.pdf](#)
[PS-76060-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Backplane Connectors
Series	76450
Description	Impact 100 Ohm 2 Pair Right-Angle Male Header, Right Guided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free
Application	Coplanar
Component Type	PCB Header
Product Name	Impact
UPC	883906873776

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shield Type	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	8.912/g
Number of Columns	10
Number of Pairs	2
Number of Rows	6
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	1.20mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacles	<u>76460</u>

This document was generated on Mar 03, 2025
