


# HC-DD108-I-CT-M - Contact insert



1584114

<https://www.phoenixcontact.com/us/products/1584114>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 108+PE, size: B24, number of connections per position: 1, Pin, Crimp connection, 250 V, 10 A, 0.14 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, application: Signal

## Your advantages

- Can be used in rail vehicles, satisfy DIN EN 45545-2 with requirement sets R22, R23, and R24 in hazard levels HL1, HL2, and HL3.
- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

Item number	1584114
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF61
Product key	AF7ABF
Catalog page	Page 539 (C-2-2019)
GTIN	4046356133425
Weight per piece (including packing)	67.4 g
Weight per piece (excluding packing)	66.3 g
Customs tariff number	85389099
Country of origin	CN

# HC-DD108-I-CT-M - Contact insert

1584114

<https://www.phoenixcontact.com/us/products/1584114>



## Technical data

### Notes

General	For housing HC-B24
General	Connectors may be operated only when there is no load/voltage.
General	It is imperative that guide pins (HC-CST) and sockets (HC-CBU) are used to prevent tip collision due to misalignment.

### Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---


### Product properties

Product type	Contact insert with a fixed no. of positions
Series	HC-DD
Application	Signal
Type	B24
	B48
Number of positions	108
Connection profile	108+PE
Contact numbering	1 - 108
Number of connections per position	1
Contact material type	turned
	rolled

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Dimensions

Dimensional drawing	
Width	34 mm
Height	32.5 mm
Length	111 mm
Drill hole distance, horizontal	104 mm
Drill hole distance, vertical	27 mm

### Mechanical characteristics

Minimum housing height	72 mm
Contact diameter	1.6 mm

# HC-DD108-I-CT-M - Contact insert



1584114

<https://www.phoenixcontact.com/us/products/1584114>

## Connection data

### Connection technology

Connection technology	Crimp connection
Number of connections per position	1
Connection in acc. with standard	IEC / EN

### Conductor connection

Conductor cross section	0.14 mm² ... 2.5 mm²
Connection cross section AWG	26 ... 14
Tightening torque	0.8 Nm ... 1.2 Nm (PE connection) 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing)
Stripping length of the individual wire	8 mm (0.14 mm² ... 1.5 mm²) 6 mm (2.5 mm²)

## Electrical properties

Rated voltage (III/3)	250 V
Rated surge voltage	4 kV
Rated current	10 A
SCCR	5 kA (UL 2237)

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Material specifications

Flammability rating according to UL 94	V0
Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC
Standards/regulations	PC

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--

## Standards and regulations

Constructional and testing regulations	DIN VDE 0627/86 DIN VDE 0110/02.79 DIN VDE 0110-1/04.97 IEC 60664-1, DIN IEC 60512 IEC 60352 DIN VDE 0627/86
--	---

# HC-DD108-I-CT-M - Contact insert



1584114

<https://www.phoenixcontact.com/us/products/1584114>

Tests	DIN VDE 0110/02.79
	DIN VDE 0110-1/04.97
	IEC 60664-1, DIN IEC 60512
	IEC 60352

Testing

Standards/regulations	PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3)
-----------------------	---

# HC-DD108-I-CT-M - Contact insert




1584114

<https://www.phoenixcontact.com/us/products/1584114>


## Drawings

Dimensional drawing



## Male insert

Dimensional drawing



Mounting cutout when used without housing


# HC-DD108-I-CT-M - Contact insert

1584114

<https://www.phoenixcontact.com/us/products/1584114>



Schematic diagram



Connector pin assignment, connection side


# HC-DD108-I-CT-M - Contact insert

1584114

<https://www.phoenixcontact.com/us/products/1584114>




Diagram



Derating diagram turned contacts

Diagram



Derating diagram rolled contacts

# HC-DD108-I-CT-M - Contact insert



1584114

<https://www.phoenixcontact.com/us/products/1584114>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1584114>

### DNV

Approval ID: TAE000037S



### CSA

Approval ID: 013631\_6233\_01

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	250 V	7 A	26 - 14	-



### cUL Recognized

Approval ID: E118976

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	250 V	7 A	- 14	-



### UL Recognized

Approval ID: E118976

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	250 V	10 A	- 14	-



### cULus Recognized

Approval ID: E468743

	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	250 V	7 A	- 14	-



# HC-DD108-I-CT-M - Contact insert



1584114

<https://www.phoenixcontact.com/us/products/1584114>

## Classifications

### ECLASS

ECLASS-13.0	27440205
-------------	----------

### ETIM

ETIM 9.0	EC000438
----------	----------

### UNSPSC

UNSPSC 21.0	39121500
-------------	----------

# HC-DD108-I-CT-M - Contact insert



1584114  
<https://www.phoenixcontact.com/us/products/1584114>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)