



PENE5GAL, Oxide Inhibitor, 5 Gallon Container

By Burndy
Catalog # [PENE5GAL](#)

Electrical Joint Compound, 5 Gallon Steel Pail, 28/26 Gauge-Black, For Cu/Cu Applications ,Grounding, Cu Conduit Threads



Features

- PENETROX™ Oxide Inhibiting Joint Compounds are available in many types
- PENETROX A is a natural compound recommended for aluminum to aluminum, aluminum to copper connections and aluminum conduit threads, it is not recommended for use with rubber or polyethylene insulated conductors
- PENETROX A13 is a synthetic base compound with evenly suspended zinc particles recommended for aluminum to aluminum, aluminum to copper, and also aluminum conduit threads
- PENETROX E is a synthetic base with evenly suspended copper particles, recommended for copper to copper, copper threads, and all grounding applications

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	Yes

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Package Height	0.000 in

General

Trade Name	PENETROX™
Application - For Use On	Copper to Copper
Pour Point	-40 °F
UPC 12 Digit	781810023617
UPC 14 Digit GTIN	00781810023617
Container Type	Pail
UPC	781810023617

Logistics

Minimum Pack Quantity	1
Container Size	5 Gallon
Carton Quantity	1
Pallet Quantity	180

Operational

Temperature - Dropping Point	350 °F
Fahrenheit	
Viscosity at 100 Fahrenheit	250 °F

Product Assets

[Catalog \[English\]](#)