




**Part Number :** [191930204](#)  
**Product Description :** VersaKrimp Ring  
Tongue Terminal for 8 AWG Wire, Closed-  
Brazed Barrel, Stud Size 1/4" (M6), Carton  
**Series Number :** 19193  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** D-356-14



## Documents & Resources

**Drawings**  
[191930204\\_sd.pdf](#)

**3D Models and Design Files**  
[191930204\\_stp.zip](#)

**Specifications**  
[PS-19902-011-001.pdf](#)  
[PS-19902-013-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC  
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Type	Ring
UPC	800755050561

#### Agency

CSA	LR18689
UL	E32244

#### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.696/g
Packaging Type	Carton
Stud Size	1/4" (M6)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	7.19mm max.
Wire Size (AWG)	8
Wire Size mm <sup>2</sup>	10.00

---

## Application Tooling

### Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192900001</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
RHT1080 Hand Crimp Tool	<u>640034400</u>
Square "DIN" style dies for 8 AWG	<u>640037670</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640074400</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>

---

This document was generated on Mar 09, 2025