



Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers > AMP Carrier for Receptacle Inserts



Number of Positions: 36

Primary Product Color: Blue

Protection & Strain Relief Accessory Type: Cover Assembly

Primary Product Material: PBT GF

Cable Exit Angle: 180°

[All AMP Carrier for Receptacle Inserts \(14\)](#)

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover Assembly
---	----------------

Configuration Features

Compatible With Connector Code	D
Number of Positions	36

Body Features

Primary Product Color	Blue
Primary Product Material	PBT GF
Cable Exit Angle	180°

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[248 °F]
-----------------------------	--



Operating Temperature Range

-40 – 120 °C[-40 – 248 °F]

Packaging Features

Packaging Method	Box
Packaging Quantity	900

Other

Serviceable	No
-------------	----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-1718492-4
1.5MM TAB HSG 36 POS ASSY



TE Part # CAT-AM705-CH8173
AMP Unsealed Connector Housing




TE Part # 2-1718486-4
CARRIER FOR RECEPT.INSERT 25
POS 36 POS

Also in the Series | AMP MCP Connector System



Automotive Connector Locks &
Position Assurance(5)




Automotive Housings(237)



Automotive Seals & Cavity Plugs(6)



Automotive Signal & Power Connector
Housings(83)



Other Automotive Connector
Accessories(4)

Customers Also Bought




TE Part #CAT-T4827-CH8172
Timer Connector Housing



TE Part #CAT-M4599-B128
AMP Carrier for Receptacle Inserts



TE Part #CAT-AM705-CH8173
AMP Unsealed Connector Housing



TE Part #175063-1
040 MULTILOCK TAB CONT. L/P

Documents

Product Drawings

CARRIER FOR RECEPT INSERTS 36 POS

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-1718485-4_D.2d_dxf.zip

1-1718485-4

36 Position, Blue, Cover Assembly, PBT GF, 180° Cable Exit, -40 – 120 °C [-40 – 248 ° F], AMP MCP Connector System



English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1718485-4_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1718485-4_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

German