



Color: ■ white

Dimensions in mm
 Plate thickness: 0.5 ... 2 mm Cutout tolerance: + 0.1 mm Please note!

Cover WINSTA® MINI 3-pole

Put your trust in reliable safety for the electrical installation in your project: The cover from the WINSTA® MINI product line. An extensive range of accessories complements the WINSTA® product line from WAGO. Due to its particularly compact dimensions, our WINSTA® MINI Pluggable Connection System with Push-in CAGE CLAMP® spring pressure connection technology is specifically suitable in very tight spaces, i.e., for connections when very little room is available.

Push-in CAGE CLAMP® spring pressure connection technology – pluggable installation instead of laborious screw connections!

WINSTA® is the pluggable connection system that is ideally tailored to the strict requirements of electrical installation. It ensures error-free installation of cables and components, quickly and reliably. Now you can also cut installation expenses without compromising quality and safety: with protection against mismatching reduces the need for servicing and prevents unnecessary downtime.

- consistent IP40 protection
- quick replacement of defective units during ongoing operation

Notes

General safety information

NOTICE: Observe installation and safety instructions!

1. Only to be used by a qualified electrician or by a person electrically instructed for the task (EIP per DIN VDE 0105-100).
2. Do not install while energized or under load.
3. Use only for its intended purpose.
4. Observe applicable national regulations, standards and directives.
5. Observe the technical specifications of the products.
6. Ensure correct polarity assignment.
7. Do not use damaged or contaminated components.
8. Observe conductor types, conductor cross-sections, strip lengths and cable diameters.
9. Insert conductors up to the stop.
10. Use only with locking lever and strain relief.
11. Use original accessories only.

To be sold only with installation instructions!

Note

The snap-in connectors must be relieved of tensile and transverse forces. A surface finish can influence the edge radius of the cutouts. This may affect the snap-in socket fit, so ensure an adequate fit before use. In addition, the punched edge should be on the inside for punched cutouts. The wings of the snap-in connectors must not be mechanically stressed for a long period before use (e.g., due to a pre-locking position).

Connection Data

Connection 1

Pole number	3
-------------	---

Physical data

Width	21.6 mm / 0.85 inches
Height	16 mm / 0.63 inches
Depth	10.1 mm / 0.398 inches

Mechanical data

Mounting type	Snap-in flange
Suitable	for cutout

Material data

Note (material data)	Information on material specifications can be found here
Color	white
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.037 MJ
Weight	1.4 g

Environmental requirements

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

Product Group	20 (Winsta)
PU (SPU)	100 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454526528
Customs tariff number	39269097900

Product Classification

UNSPSC	39121702
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 9.0	EC002863
ETIM 10.0	EC002863
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

Compliance Search	
Environmental Product Compliance 890-693	↓

Documentation

Bid Text			
890-693	19.02.2019	xml 2.56 KB	↓
890-693	26.11.2014	doc 22.50 KB	↓

CAD/CAE-Data

CAD data	
2D/3D Models 890-693	↓

CAE data	
WSCAD Universe 890-693	↓
ZUKEN Portal 890-693	↓

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at: www.wago.com