

Powered-off Isolation, 0.86 Ω , 1.65 V to 5.5 V, SPDT Analog Switch (2:1 Multiplexer)

DESCRIPTION

The DG4157E is a high performance single-pole, double-throw (SPDT) analog switch designed for 1.65 V to 5.5 V operation with a single power rail. Fabricated with high density CMOS technology, the device achieves low on resistance of 0.86 Ω at a 4.5 V power supply, low power consumption, and fast switching speeds. The DG4157E can handle both analog and digital signals and permits signals with amplitudes of up to V_+ to be transmitted in either direction. Its control logic inputs can go over V_+ up to 5.5 V. The control logic input high threshold is guaranteed as low as 1.8 V over the power supply range up to 5.5 V. It features break before make switching performance. Its -3 dB bandwidth is typically 152 MHz. A powered-off protection circuit is built into the switch to prevent an abnormal current flow from COM pin to V_+ during the power-down condition. Each output pin can withstand greater than 7 kV (human body model). Operation temperature is specified from -40 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$. The DG4157E is available in the ultra compact $\mu\text{DFN-6L}$ and SC-70-6 packages.

FEATURES

- Low switch on-resistance (0.86 Ω)
- 1.65 V to 5.5 V single supply operation
- Isolation in powered-off mode
- Guaranteed 1.8 V logic high
- Control logic inputs can go over V_+
- Low charge injection (5 pC)
- Low total harmonic distortion
- Break before make switching
- Latch-up performance exceeds 300 mA per JESD 78
- ESD tested
 - 7000 V human body model (JS-001)
 - 1000 V charge device model (JS-002)
- Ultra compact $\mu\text{DFN-6L}$ 1 mm x 1 mm x 0.35 mm package
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912







RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Smartphones and tablets
- Consumer and computing
- Portable instrumentation
- Medical equipment

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



TRUTH TABLE	
LOGIC INPUT (S)	FUNCTION
0	B_0 connected to A
1	B_1 connected to A

ORDERING INFORMATION		
TEMP. RANGE	PACKAGE	PART NUMBER
-40 $^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$	SC-70-6L	DG4157EDL-T1-GE3
	$\mu\text{DFN-6L}$	DG4157EDN-T1-GE4

**ABSOLUTE MAXIMUM RATINGS**

PARAMETER		LIMIT	UNIT
V+, A, B ₀ , B ₁ , S reference to GND		-0.3 to 6	V
Continuous current (any terminal)		± 200	mA
Peak current (pulsed at 1 ms, 10 % duty cycle)		± 400	
Thermal resistance ^a		407	°C/W
ESD / HBM	JS-001	7000	V
ESD / CDM	JS-002	1000	
Latch up	JESD78	300	mA
Operating temperature		-40 to +85	°C
Max. operating junction temperature		150	
Operating junction temperature		125	
Storage temperature		-65 to +150	

Note

a. Measured on an 1" x 1" inch FR4 board, using 0.39" by 1", 2 oz. copper trace without air flow

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V+ = 3 V, V _S = 0 V or V+ ^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT
				MIN. ^b	TYP. ^c	MAX. ^b	
DC Characteristics							
On resistance	R _{ON}	V+ = 2.7 V, B ₀ or B ₁ = 1.5 V, I _O = 100 mA	Room	-	1.6	2	Ω
			Full	-	-	3	
		V+ = 4.5 V, B ₀ or B ₁ = 3.5 V, I _O = 100 mA	Room	-	0.86	1.2	
			Full	-	-	1.5	
On resistance flatness	R _{FLATNESS}	V+ = 2.7 V, B ₀ or B ₁ = 0.75 V, 1.5 V, I _O = 100 mA	Room	-	0.2	-	
			Full	-	-	-	
		V+ = 4.5 V, B ₀ or B ₁ = 1 V, 3.5 V, I _O = 100 mA	Room	-	0.05	0.3	
			Full	-	-	0.4	
On resistance match	ΔR _{ON}	V+ = 2.7 V, B ₀ or B ₁ = 1.5 V, I _O = 100 mA	Room	-	0.003	-	
			Full	-	-	-	
		V+ = 4.5 V, B ₀ or B ₁ = 3.5 V, I _O = 100 mA	Room	-	0.004	0.12	
			Full	-	-	0.15	
Switch off leakage current	I _{OFF}	V+ = 5.5 V, A = 1 V, 4.5 V B ₀ or B ₁ = 4.5 V, 1 V or floating	Room	-3	1.36	3	nA
Switch on leakage current	I _{ON}		Full	-20	-	20	
			Room	-4	1.4	4	
			Full	-40	-	40	
Power down leakage	I _{A(DP)}	V+ = 0 V, V _A = 4.5 V, V _S = GND	Full	-1	-	1	μA
Digital Control							
Input, high voltage	V _{INH}	V+ = 2.7 V to 5.5 V	Full	1.8	-	-	V
Input, low voltage	V _{INL}		Full	-	-	0.6	
Input current	I _{INH} , I _{INL}	V _S = 0 or V+	Full	-1	-	1	μA




SPECIFICATIONS							
PARAMETER	SYMBOL	TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V+ = 3 V, VS = 0 V or V+ ^e	TEMP. ^a	LIMITS -40 °C to +85 °C			UNIT
				MIN. ^b	TYP. ^c	MAX. ^b	
AC Characteristics							
Turn-on time ^d	tON	V+ = 2.7 V, B0 or B1 = 1.5 V, RL = 50 Ω, CL = 35 pF	Room	-	27	42	ns
			Full	-	-	47	
		V+ = 4.5 V, B0 or B1 = 1.5 V, RL = 50 Ω, CL = 35 pF	Room	-	17	32	
			Full	-	-	35	
Turn-off time ^d	tOFF	V+ = 2.7 V, B0 or B1 = 1.5 V, RL = 50 Ω, CL = 35 pF	Room	-	16	32	
			Full	-	-	35	
		V+ = 4.5 V, B0 or B1 = 1.5 V, RL = 50 Ω, CL = 35 pF	Room	-	11	28	
			Full	-	-	30	
Break-before-make time ^d	tBBM	V+ = 2.7 V, B0 = B1 = 1.5 V, RL = 50 Ω, CL = 35 pF	Room	1	13	-	
		V+ = 4.5 V, B0 = B1 = 1.5 V, RL = 50 Ω, CL = 35 pF		1	8	-	
Charge injection ^d	Q	CL = 1 nF, RGEN = 0 Ω, VGEN = 0 V	Room	-	-5	-	pC
Off isolation ^d	OIRR	RL = 50 Ω, f = 1 MHz	Room	-	-64	-	dB
		RL = 50 Ω, f = 10 MHz		-	-41	-	
Crosstalk ^d	XTALK	RL = 50 Ω, CL = 5 pF, f = 1 MHz	Room	-	-64	-	
		RL = 50 Ω, CL = 5 pF, f = 10 MHz		-	-41	-	
Bandwidth ^d	BW	RL = 50 Ω	Room	-	152	-	MHz
Total harmonic distortion ^d	THD	RL = 600 Ω, VSIGNAL = 0.5 V, f = 20 Hz to 20 kHz	Room	-	0.0055	-	%
Capacitance							
BX port off capacitance ^d	CB(OFF)	RL = 50 Ω, CL = 5 pF, f = 1 MHz	Room	-	13	-	pF
A port on capacitance ^d	CA(ON)			-	52	-	
Control pin capacitance ^d	CIN			-	1	-	
Power Supply							
Quiescent supply current	I+	V+ = 5.5 V, VS = 0 V, 5.5 V	Room	-	0.0004	0.8	μA
			Full	-	-	1	

Notes


- a. Room = 25 °C, full = as determined by the operating suffix
b. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet
c. Typical values are for design aid only, not guaranteed nor subject to production testing
d. Guarantee by design, nor subjected to production test
e. V_S = input voltage to perform proper function




TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$, unless otherwise noted)




R_{ON} vs. V_A and Supply Voltage




R_{ON} vs. V_A and Supply Voltage




R_{ON} vs. V_A and Temperature



R_{ON} vs. V_A and Temperature




Leakage Current vs. Analog Voltage




Leakage Current vs. Temperature




TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$, unless otherwise noted)




Supply Current vs. Temperature




Supply Current vs. Temperature




Insertion Loss, Off-Isolation, Crosstalk vs. Frequency








Supply Current vs. Switching Frequency




Switching Time vs. Temperature








Switching Threshold vs. Supply Voltage

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$, unless otherwise noted)

Charge Injection vs. Source Voltage

THD+N vs. Frequency

Supply Current vs. Logic Voltage

Power Down Leakage Current vs. Temperature

Power Down Leakage Current vs. V_A

TEST CIRCUITS

 C_L (includes fixture and stray capacitance)



$$V_{OUT} = V_A \left(\frac{R_L}{R_L + R_{ON}} \right)$$


Fig. 1 - Switching Time

 C_L (includes fixture and stray capacitance)

Fig. 2 - Break-Before-Make Interval


$$Q = \Delta V_{OUT} \times C_L$$

S depends on switch configuration: input polarity determined by sense of switch.

Fig. 3 - Charge Injection

TEST CIRCUITS

Fig. 4 - Off-Isolation

Fig. 5 - Channel Off/On Capacitance





PRODUCT SUMMARY		
Part number	DG4157E	DG4157E
Status code	2	2
Configuration	SPDT x 2	SPDT x 2
Single supply min. (V)	1.65	1.65
Single supply max. (V)	5.5	5.5
Dual supply min. (V)	-	-
Dual supply max. (V)	-	-
On-resistance (Ω)	0.86	0.86
Charge injection (pC)	-5	-5
Source on capacitance (pF)	52	52
Source off capacitance (pF)	13	13
Leakage switch on typ. (nA)	1.4	1.4
Leakage switch off max. (nA)	3	3
-3 dB bandwidth (MHz)	152	152
Package	SC-70-6	μ DFN-6
Functional circuit / applications	Multi Purpose, instrumentation, medical and healthcare, portable	Multi Purpose, instrumentation, medical and healthcare, portable
Interface	Parallel	Parallel
Single supply operation	Yes	Yes
Dual supply operation	-	-
Turn on time max. (ns)	47	47
Crosstalk and off isolation	-41	-41

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?75778.




SC-70: 6-LEADS



Dim	MILLIMETERS			INCHES		
	Min	Nom	Max	Min	Nom	Max
A	0.90	—	1.10	0.035	—	0.043
A ₁	—	—	0.10	—	—	0.004
A ₂	0.80	—	1.00	0.031	—	0.039
b	0.15	—	0.30	0.006	—	0.012
c	0.10	—	0.25	0.004	—	0.010
D	1.80	2.00	2.20	0.071	0.079	0.087
E	1.80	2.10	2.40	0.071	0.083	0.094
E ₁	1.15	1.25	1.35	0.045	0.049	0.053
e	0.65BSC			0.026BSC		
e ₁	1.20	1.30	1.40	0.047	0.051	0.055
L	0.10	0.20	0.30	0.004	0.008	0.012
α	7°Nom			7°Nom		

ECN: S-03946—Rev. B, 09-Jul-01
DWG: 5550

μDFN-6L 1 mm x 1 mm Case Outline




DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.32	0.35	0.38	0.013	0.014	0.015
A1	0.00	-	0.05	0.000	-	0.002
A2	0.10 Ref.			0.004 Ref.		
b	0.12	0.15	0.18	0.005	0.006	0.007
D	0.95	1.00	1.05	0.037	0.039	0.041
E	0.95	1.00	1.05	0.037	0.039	0.041
e	0.35 BSC			0.014 BSC		
K	0.30 Ref.			0.012 Ref.		
K1	0.075 Ref.			0.003 Ref.		
K2	0.05 Ref.			0.002 Ref.		
L	0.27	0.30	0.33	0.011	0.012	0.013

ECN: E23-0309-Rev. B, 28-Aug-2023
DWG: 6053

Notes

- Use millimeters as the primary measurement
- Dimensioning and tolerances conform to ASME Y14.5M-1994
- N is the number of terminals
- Nd and Ne is the number of terminals in each D and E site respectively
- Dimensions b applies to plated terminal and is measured between 0.15 mm and 0.30 mm from terminal tip
- The pin 1 identifier must be existed on the top surface of the package by using indentation mark or other feature of package body
- Package warpage max. 0.05 mm

Recommended Minimum PADs for μ DFN 6L



Mounting Footprint
Dimensions in mm



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.