





DATE	REV	ECN	APP'D. BY
11-13-15	A15	10215	TRM
3-16-16	A16	10614	TRM



LED SPECIFICATIONS			
STANDARD LED	* FORWARD VOLTAGE (MAX)	* FORWARD VOLTAGE (TYP)	WAVELENGTH
GREEN DIFFUSED	2.6 V	2.25 V	565 nm
YELLOW DIFFUSED	2.5 V	2.1 V	590 nm
RED DIFFUSED	2.5 V	2.0 V	625 nm


* WITH A FORWARD CURRENT OF 20 mA

LED POLARITY
(ENLARGED VIEW)




SINGLE COLOR LED

LED POLARITY
(ENLARGED VIEW)



BI-COLOR LED


LED POLARITY
(ENLARGED VIEW)




BI-COLOR LED

MATERIAL:
HOUSING: PBT+30%G.F. UL94V-0. STANDARD COLOR: BLACK
INSERT: PBT+30%G.F. UL94V-0. STANDARD COLOR: BLACK
LENS: PC UL94V-0. STANDARD COLOR: CLEAR
BACK: PBT+30%G.F. STANDARD COLOR: BLACK
LED 3.2 x 2.0 x 4.0 x P=2.29mm.
SHIELD: COPPER ALLOY 0.25mm THICKNESS.
CONTACT: 0.35mm (.014") THICKNESS, 50 MICRO INCH
SELECTIVE GOLD PLATING OVER
NICKEL PHOSPHOR BRONZE ALLOY.
FOR PRODUCT SPECIFICATION SEE PR022-01


GREEN/YELLOW	GREEN/YELLOW	SS-74401-011
GREEN	RED	SS-74401-008
YELLOW	GREEN	SS-74401-001
POSITION 2	POSITION 1	PART NUMBER
INDICATOR COLOR		



P.C.B. RECOMMENDED HOLE LAYOUT
SEEN FROM COMPONENT SIDE
TOLERANCE ±.003 [0.08] UNLESS OTHERWISE SPECIFIED



RoHS



DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]
UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ± 1°
SHEET NO. 1 OF 1



TITLE: MODULAR JACKS, EMI-RFI ONE PIECE SHIELDED, ESD GROUND
SINGLE PORT PCB, LED PAC

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF
STEWART CONNECTOR AND SHALL NOT BE REPRODUCED,
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN
CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS
MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE
VISIT: HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/

DRN BY: TRM DATE 9-26-01
APPD BY: RGC DATE 9-26-01
DWG NO. CT740080 REV. A16

11118 Susquehanna Trail South
Glen Rock, PA 17327-9199
(717) 235-7512
http://www.stewartconnector.com