

# PC817XxNSZ2B Series

DIP 4pin  
Photocoupler



## ■ Description

**PC817XxNSZ2B Series** contains an IRED optically coupled to a phototransistor.  
It is packaged in a 4-pin DIP.  
Input-output isolation voltage(rms) is 5kV.  
Collector-emitter voltage is 80V.  
CTR is 50% to 600% (at  $I_F=5\text{mA}$ ,  $V_{CE}=5\text{V}$ ,  $T_a=25^\circ\text{C}$ )

## ■ Features

1. 4-pin DIP package
2. Double transfer mold package  
(Ideal for Flow Soldering)
3. High isolation voltage between input and output  
(Viso(rms) : 5kV)
4. High collector-emitter voltage( $V_{CEO}$  : 80V)
5. Current transfer ratio  
(CTR : MIN. 50% at  $I_F=5\text{ mA}$ ,  $V_{CE}=5\text{V}$ ,  $T_a=25^\circ\text{C}$ )
6. RoHS directive compliant

## ■ Agency approvals/Compliance


1. Recognized by UL1577 (Double protection isolation),  
file No. E64380 (as model No. **PC817**)
2. Approved by CSA  
file No. CA95323 (as model No. **PC817**)
3. Package resin : UL flammability grade (94V-0)

## ■ Applications


1. Programmable controllers
2. Facsimiles
3. Telephones

Notice The content of data sheet is subject to change without prior notice.  
In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.

Sheet No.: OP18022EN  
DATE Nov.05.2018  
© SHARP Corporation

**■ Internal Connection Diagram****■ Outline**

(Unit : mm)



**Date code indication (Ex.)**

3-digit number shall be marked the age indication of 1-digit number, and week code of 2-digit number.

Week code "01" indicate the week including the first Thursday of January. And later, Monday is the starting point.

| Year | Week |
|------|------|
|      |      |

| Date code | MON   | TUE   | WED   | THU   | FRI   | SAT   | SUN   |
|-----------|-------|-------|-------|-------|-------|-------|-------|
| 652       | 12/26 | 12/27 | 12/28 | 12/29 | 12/30 | 12/31 | 1/1   |
| 701       | 1/2   | 1/3   | 1/4   | 1/5   | 1/6   | 1/7   | 1/8   |
| 702       | 1/9   | 1/10  | 1/11  | 1/12  | 1/13  | 1/14  | 1/15  |
| 703       | 1/16  | 1/17  | 1/18  | 1/19  | 1/20  | 1/21  | 1/22  |
| .         | .     | .     | .     | .     | .     | .     | .     |
| .         | .     | .     | .     | .     | .     | .     | .     |
| .         | .     | .     | .     | .     | .     | .     | .     |
| 752       | 12/11 | 12/12 | 12/13 | 12/14 | 12/15 | 12/16 | 12/17 |
| 751       | 12/18 | 12/19 | 12/20 | 12/21 | 12/22 | 12/23 | 12/24 |
| 752       | 12/25 | 12/26 | 12/27 | 12/28 | 12/29 | 12/30 | 12/31 |
| 801       | 1/1   | 1/2   | 1/3   | 1/4   | 1/5   | 1/6   | 1/7   |

**Factory identification mark and Plating material**

| Factory identification Mark | Country of origin | Plating material |
|-----------------------------|-------------------|------------------|
| T                           | Taiwan            | Sn               |

**Rank mark**

Refer to the Model Line-up table.

## ■ Absolute Maximum Ratings

(T<sub>a</sub>=25°C)

| Parameter                            |                                     | Symbol                 | Rating      | Unit |
|--------------------------------------|-------------------------------------|------------------------|-------------|------|
| Input                                | Forward current                     | I <sub>F</sub>         | 50          | mA   |
|                                      | * <sup>1</sup> Peak forward current | I <sub>FM</sub>        | 1           | A    |
|                                      | Reverse voltage                     | V <sub>R</sub>         | 6           | V    |
|                                      | Power dissipation                   | P                      | 70          | mW   |
| Output                               | Collector-emitter voltage           | V <sub>CEO</sub>       | 80          | V    |
|                                      | Emitter-collector voltage           | V <sub>ECO</sub>       | 6           | V    |
|                                      | Collector current                   | I <sub>C</sub>         | 50          | mA   |
|                                      | Collector power dissipation         | P <sub>C</sub>         | 150         | mW   |
| Total power dissipation              |                                     | P <sub>tot</sub>       | 200         | mW   |
| * <sup>2</sup> Isolation voltage     |                                     | V <sub>iso</sub> (rms) | 5           | kV   |
| Operating temperature                |                                     | T <sub>opr</sub>       | -30 to +100 | °C   |
| Storage temperature                  |                                     | T <sub>stg</sub>       | -55 to +125 | °C   |
| * <sup>2</sup> Soldering temperature |                                     | T <sub>sol</sub>       | 270         | °C   |

\*1 Pulse width≤100μs, Duty ratio : 0.001

\*2 40 to 60%RH, AC for 1 minute

\*3 For 10s

## ■ Electro-optical Characteristics

(T<sub>a</sub>=25°C)


| Parameter                        |                                      | Symbol               | Condition  | MIN.   | TYP.               | MAX. | Unit |
|----------------------------------|--------------------------------------|----------------------|--|--|--------------------|------|------|
| Input                            | Forward voltage                      | V <sub>F</sub>       | I <sub>F</sub> =20mA   | —  | 1.2                | 1.4  | V    |
|                                  | Peak forward voltage                 | V <sub>FM</sub>      | I <sub>FM</sub> =0.5A  | —  | —                  | 3.0  | V    |
|                                  | Reverse current                      | I <sub>R</sub>       | V <sub>R</sub> =4V   | —  | —                  | 10   | μA   |
|                                  | Terminal capacitance                 | C <sub>t</sub>       | V=0, f=1kHz  | —  | 30                 | 250  | pF   |
| Output                           | Dark current                         | I <sub>CEO</sub>     | V <sub>CE</sub> =50V, I <sub>F</sub> =0                              | —  | —                  | 100  | nA   |
|                                  | Collector-emitter breakdown voltage  | BV <sub>CEO</sub>    | I <sub>C</sub> =0.1mA, I <sub>F</sub> =0                             | 80   | —                  | —    | V    |
|                                  | Emitter-collector breakdown voltage  | BV <sub>ECO</sub>    | I <sub>E</sub> =10μA, I <sub>F</sub> =0                              | 6  | —                  | —    | V    |
| Transfer<br>charac-<br>teristics | Collector current                    | I <sub>C</sub>       | I <sub>F</sub> =5mA, V <sub>CE</sub> =5V                             | 2.5  | —                  | 30   | mA   |
|                                  | Collector-emitter saturation voltage | V <sub>CE(sat)</sub> | I <sub>F</sub> =20mA, I <sub>C</sub> =1mA                            | —  | 0.1                | 0.2  | V    |
|                                  | Isolation resistance                 | R <sub>iso</sub>     | DC500V, 40 to 60%RH  | 5×10 <sup>10</sup>   | 1×10 <sup>11</sup> | —    | Ω    |
|                                  | Floating capacitance                 | C <sub>f</sub>       | V=0, f=1MHz  | —  | 0.6                | 1.0  | pF   |
|                                  | Cut-off frequency                    | f <sub>C</sub>       | V <sub>CE</sub> =5V, I <sub>C</sub> =2mA, R <sub>L</sub> =100Ω, -3dB | —  | 80                 | —    | kHz  |
|                                  | Response time                        | Rise time            | t <sub>r</sub>   | V <sub>CE</sub> =2V, I <sub>C</sub> =2mA, R <sub>L</sub> =100Ω |                    |      | 4    |
|                                  |                                      | Fall time            | t <sub>f</sub>   |  |                    |      | 3    |

**■ Model Line-up**


| Lead Form | Through-Hole        | Rank mark   | I <sub>c</sub> [mA]       | CTR[%]    |
|-----------|---------------------|-------------|---------------------------|-----------|
| Package   | Sleeve              |             | (IF=5mA, VCE=5V, Ta=25°C) |           |
|           | 100pcs/sleeve       |             |                           |           |
| Model No. | <b>PC817XNNSZ2B</b> | with or “_” | 2.5 ~ 30                  | 50 ~ 600  |
|           | <b>PC817X1NSZ2B</b> | A           | 4.0 ~ 8.0                 | 80 ~ 160  |
|           | <b>PC817X2NSZ2B</b> | B           | 6.5 ~ 13                  | 130 ~ 260 |
|           | <b>PC817X3NSZ2B</b> | C           | 10 ~ 20                   | 200 ~ 400 |
|           | <b>PC817X4NSZ2B</b> | D           | 15 ~ 30                   | 300 ~ 600 |

Please contact a local SHARP sales representative to inquire about production status.


**Fig.1 Forward Current vs. Ambient Temperature**




**Fig.2 Diode Power Dissipation vs. Ambient Temperature**




**Fig.3 Collector Power Dissipation vs. Ambient Temperature**




**Fig.4 Total Power Dissipation vs. Ambient Temperature**




**Fig.5 Peak Forward Current vs. Duty Ratio**




**Fig.6 Forward Current vs. Forward Voltage**




**Fig.7 Current Transfer Ratio vs. Forward Current**




**Fig.8 Collector Current vs. Collector-emitter Voltage**




**Fig.9 Relative Current Transfer Ratio vs. Ambient Temperature**




**Fig.10 Collector - emitter Saturation Voltage vs. Ambient Temperature**




**Fig.11 Collector Dark Current vs. Ambient Temperature**




**Fig.12 Collector-emitter Saturation Voltage vs. Forward Current**




**Fig.13 Response Time vs. Load Resistance**




**Fig.15 Frequency Response**



**Fig.14 Test Circuit for Response Time**



**Fig.16 Test Circuit for Frequency Response**



Remarks : Please be aware that all data in the graph are just for reference and not for guarantee.

**■ Design Considerations****• Design guide**

While operating at  $I_F < 1\text{mA}$ , CTR variation may increase.

Please make design considering this fact.

This product is not designed against irradiation and incorporates non-coherent IRED.

**• Degradation**

In general, the emission of the IRED used in photocouplers will degrade over time.

In the case of long term operation, please take the general IRED degradation (50% degradation over 5 years) into the design consideration.

**■ Manufacturing Guidelines****• Soldering Method****Flow Soldering :**

Due to SHARP's double transfer mold construction submersion in flow solder bath is allowed under the below listed guidelines.

Flow soldering should be completed below 270°C and within 10s.

Preheating is within the bounds of 100 to 150°C and 30 to 80s.

Please don't solder more than twice.

**Hand soldering**

Hand soldering should be completed within 3s when the point of solder iron is below 400°C.

Please don't solder more than twice.

**Other notice**

Please test the soldering method in actual condition and make sure the soldering works fine, since the impact on the junction between the device and PCB varies depending on the tooling and soldering conditions.

- **Cleaning instructions**

**Solvent cleaning :**

Solvent temperature should be 45°C or below. Immersion time should be 3 minutes or less.

**Ultrasonic cleaning :**

The impact on the device varies depending on the size of the cleaning bath, ultrasonic output, cleaning time, size of PCB and mounting method of the device.

Therefore, please make sure the device withstands the ultrasonic cleaning in actual conditions in advance of mass production.

**Recommended solvent materials :**

Ethyl alcohol, Methyl alcohol and Isopropyl alcohol.

In case the other type of solvent materials are intended to be used, please make sure they work fine in actual using conditions since some materials may erode the packaging resin.

- **Presence of ODC**

This product shall not contain the following materials.

And they are not used in the production process for this product.

Regulation substances : CFCs, Halon, Carbon tetrachloride, 1.1.1-Trichloroethane (Methylchloroform)

Specific brominated flame retardants such as the PBB and PBDE are not used in this product at all.

(1) The RoHS directive(2011/65/EU)

This product complies with the RoHS directive(2011/65/EU)

Object substances: mercury, lead, cadmium, hexavalent chromium, polybrominated biphenyls ( PBB ) and polybrominated diphenyl ethers ( PBDE )

(2) Content of six substances specified in Management Methods for Control of Pollution Caused by Electronic Information Products Regulation (Chinese : 电子信息产品污染控制管理办法).

**Marking Styles for the Names and Contents of the Hazardous Substances**

| Category     | Hazardous Substances |              |              |   |                                |                                       |
|--------------|----------------------|--------------|--------------|---|--------------------------------|---------------------------------------|
|              | Lead (Pb)            | Mercury (Hg) | Cadmium (Cd) | Hexavalent chromium (Cr <sup>6+</sup> ) | Polybrominated biphenyls (PBB) | Polybrominated diphenyl ethers (PBDE) |
| Photocoupler | ○                    | ○            | ○            | ○                                       | ○                              | ○                                     |

This table is prepared in accordance with the provisions of SJ/T 11364.

○ : Indicates that said hazardous substance contained in all of the homogeneous materials for this part is below the limit requirement of GB/T 26572.

**■ Package specification****• Sleeve package****Through-Hole****Package materials**

Sleeve : HIPS/PS or PC (with anti-static material)



Stopper : EPM

**Package method**

MAX. 100pcs. of products shall be packaged in a sleeve and both of sleeve edges shall be fixed by stoppers.

MAX. 25 sleeves (Product : 2,500pcs.) above shall be packaged in inner case and sealed by tape .

Max 2 bags(product : 5,000pcs) above shall be packaged in packing case , and put a cushioning material inside.

**Sleeve outline dimensions**

(Unit : mm)

**■ Important Notices**

· The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.

· Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.

· Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:

(i) The devices in this publication are designed for use in general electronic equipment designs such as:

- Personal computers
- Office automation equipment
- Telecommunication equipment [terminal]
- Test and measurement equipment
- Industrial control
- Audio visual equipment
- Consumer electronics

(ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection

with equipment that requires higher reliability such as:

- Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
- Traffic signals
- Gas leakage sensor breakers
- Alarm equipment
- Various safety devices, etc.

(iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:

- Space applications
- Telecommunication equipment [trunk lines]
- Nuclear power control equipment
- Medical and other life support equipment (e.g., scuba).

· If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Law of Japan, it is necessary to obtain approval to export such SHARP devices.

· This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.

· Contact and consult with a SHARP representative if there are any questions about the contents of this publication.