

Full-color Power SMD 6mm (130° Viewing Angle)



OVSPRGBCR4

Features:

- High brightness surface mount LED
- Small package outline (LxWxH) of 3.0x3.0x0.7mm.
- LED chips can be controlled separately to display various colors including white
- Compliance to automotive standard; AEC-Q101





Description:

The **OVSPRGBCR4A** is an energy-efficient packaged LED source that offers high luminance, and a long operating lifespan. This full-color power device offers a 120° viewing angle and an ultra-low profile (0.7mm) making it highly suitable for conventional lighting and specialized applications. Optional optics are offered to suit application. Please contact OPTEK for more information.

Applications:

- Automotive exterior and interior lighting
- Architectural indoor and outdoor lighting
- General lighting
- LED backlighting

Part Number	Viewing Angle	Emitted Color	Typical Intensity (mcd)	Lens Color
OVSPRGBCR4	120°	Red	5600-11250	Clear
		True Green	7150-11250	Clear
		Blue	1800-3550	Clear



**DO NOT LOOK DIRECTLY
AT LED WITH
UNSHIELDED EYES OR
DAMAGE TO RETINA MAY
OCCUR.**

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

Electrical Specifications


Absolute Maximum Ratings $T_A = 25^\circ\text{C}$

Storage Temperature Range	-40 ~ +100° C
Operating Temperature Range	-40 ~ +100° C
Reverse Voltage	5 V
DC forward current (per chip)	250 mA
Peak Pulse Current (per chip) ($T_P \leq 10$ msec, $D \leq 10\%$)	500 mA
Electrostatic Discharge (ESD Threshold [HBM])	Class 2
Moisture Sensitivity Level (IPC/JEDEC J-STD-020C)	2a / 672 Hrs
LED Junction Temperature	125° C

Optical and Electrical Characteristics ($I_F = 250$ mA, $T_A = 25^\circ\text{C}$)

SYMBOL	PARAMETER		MIN	TYP	MAX	UNITS
V_F	Forward Voltage	Red	2.0	2.3	2.8	V
		Green	3.0	3.4	3.8	V
		Blue	3.0	3.4	3.8	V
I_v	Luminous Intensity	Red	7,150	9,000	11,250	mcd
		Green	9,000	14,000	18,000	mcd
		Blue	2240	3550	5,600	mcd
λ_D	Dominant Wavelength	Red	620	625	630	nm
		Green	520	525	535	nm
		Blue	460	465	475	nm
2 $\theta_{1/2}$	Beam Angle		----	130	----	deg

Beam Angle



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.


© TT electronics plc

TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com


Issue F 07/2019 Page 2

Typical Electro-Optical Characteristics Curves


Forward Current Vs Forward Voltage (Red)




Forward Current Vs Forward Voltage (Blue and True Green)




Wavelength Shift Vs Forward Current (True Green)




Wavelength Shift Vs Forward Current (Blue)



Maximum Current Vs Solder Point Temperature



Maximum Pulse Current Vs Duty Cycle



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT electronics plc


TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

Issue F 07/2019 Page 2

Solder Pad Design


Note: Metal core circuit board (MCPCB) is highly recommended for applications.

SOLDER PAD DESIGN



Reel Dimensions: 13-inch reel

REEL DIMENSIONS (Ø 13 INCH [329])



DIMENSIONS ARE IN INCHES [MM]

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT electronics plc

TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

Issue F 07/2019 Page 2


Full-color Power SMD 6mm



OVSPRGBCR4


Carrier Tape Dimensions: Loaded quantity 2000 pieces per reel

Once inventory is depleted, the current 12 mm carrier tape and pocket will be replaced with new 8 mm carrier tape and pocket. See below specifications.




PCN 1005: New 8 mm carrier tape and pocket.

Effective: Manufacturing date codes beginning July 24, 2012



Moisture Resistant Packaging:



General Note


TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT electronics plc


TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

Issue F 07/2019 Page 2

Recommended Sn-Pb IR-Reflow Soldering Profile



Recommended Pb-free Soldering Profile



General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

© TT electronics plc

TT Electronics | OPTEK Technology
2900 E. Plano Pkwy, Plano, TX 75074 | Ph: +1 972 323 2200
www.ttelectronics.com | sensors@ttelectronics.com

Issue F 07/2019 Page 2