

Scotch® Vinyl Color Coding Electrical Tape 35, 3/4 in x 66 ft, White, 10 rolls/carton, 100 rolls/Case

Part Number 35-3/4X66FT-WH, 3M ID 7000006097, UPC 0005400708283 ★★★★★ 5.0 (3)

Details Typical Properties Resources Reviews



The combination of the pressure-sensitive, rubber-resin adhesive and the PVC backing offers excellent electrical and mechanical protection

Flame-retardant and highly resistant to UV rays, abrasion, moisture, alkalis, solvents and many acids

Suitable for use in phase identification, color-coding of motor leads and piping systems and for marking safety areas

[View more details](#)

Frequently viewed resources

[Tech Data Sheet \(PDF, 365KB\)](#)

[User Instructions \(HTML, 2KB\)](#)

[View all resources](#)

[View legal disclaimer](#)

For industrial/occupational use only. Not for consumer sale or use.

Overall Width (Metric)	19 mm
Total Tape Thickness without Liner (Metric)	0.178 mm
Overall Width (Imperial)	0.75 in
Product Color	White
Overall Length (Metric)	20.1 m
Overall Length (Imperial)	66 ft

Details

The combination of the pressure-sensitive, rubber-resin adhesive and the PVC backing offers excellent electrical and mechanical protection	Flame-retardant and highly resistant to UV rays, abrasion, moisture, alkalis, solvents and many acids	Suitable for use in phase identification, color-coding of motor leads and piping systems and for marking safety areas
Made of durable PVC	Withstands a temperature range of 14 to 221 °F (-10 to 105 °C)	UL Listed, VDE, CSA Certified and RoHS 2015/863/EU Compliant

Scotch® Vinyl Multi-Colored Electrical Tape 35 is a 7 mil thick, premium grade, electrical tape that comes in various colors. This flame retardant tape is suitable for wire and phase identification, color coding of motor leads and piping systems, and for marking safety areas. This tape is 600V rated and withstands a temperature range of 14 to 221 °F (-10 to 105 °C).

Scotch® Vinyl Multi-Colored Electrical Tape 35 provides electrical and mechanical protection with the combination of an aggressive, pressure sensitive, rubber resin adhesive and an elastic PVC backing. This tape is flame retardant and is highly resistant to UV rays, abrasion, moisture, alkalis, acids, solvents and varying weather conditions. It stretches easily and adheres virtually in any shape. Ideal for insulating electrical wires and is compatible with synthetic cable insulations, jackets and splicing compounds. UL Listed, VDE, CSA Certified and RoHS 2011/65/EU Compliant.

Typical properties

Details	
Adhesive Type	Rubber
Application	Electrical Maintenance
Backing (Carrier) Material	PVC
Brands	Scotch®
Dielectric Strength	600 V
Electrolytic Corrosion Factor	0.9
Elongation at Break	225.0 %
Flame Retardant	Yes
Insulation Resistance	> 10 ⁶ megohms
Maximum Operating Temperature (Celsius)	105 °C
Maximum Operating Temperature (Fahrenheit)	221 °F
Minimum Operating Temperature (Celsius)	0 °C
Minimum Operating Temperature (Fahrenheit)	32 °F
Product Color	White
Rolls per Carton	10
Rolls per Case	100
Shelf Life	5 Year
Specifications Met	CSA Certified, RoHS 2011/65/EU, UL Listed, VDE 0340-TEIL1
Tape Grade	Professional
Total Tape Thickness without Liner (Imperial)	7 mil
Total Tape Thickness without Liner (Metric)	0.178 mm
Voltage Rating	600 V
eClass 14 Classification Group	27144427

Dimensions and Classifications	
Overall Length (Imperial)	66 ft
Overall Length (Metric)	20.1 m
Overall Width (Imperial)	0.75 in
Overall Width (Metric)	19 mm

Resources

[Data Sheets \(1\)](#) [Brochures \(3\)](#) [Catalogs \(1\)](#) [Instructions \(1\)](#) [Product Selection Guides \(2\)](#) [Technical Papers \(1\)](#)

[Scotch® Vinyl Electrical Tape 35](#)

Data Sheets

(PDF, 365KB)

Reviews

Review Highlights

Pros

Satisfaction 2 reviews
"I bought this to tape my marching snare sticks, and I love the strength. I am buying a case to provide for the ENTIRE drumline so we can get all of our sticks taped." (Full review)

Cons

There are not enough reviews to display Cons at this time.

[SEE ALL REVIEWS](#)

Reviews

Rating Snapshot

Select a row below to filter reviews.

5 stars	3
4 stars	0
3 stars	0
2 stars	0
1 star	0

Overall Rating

5.0

★★★★★

3 Reviews

Review this Product

☆ ☆ ☆ ☆ ☆

Adding a review will require a valid email for verification

Average Customer Ratings

Quality of Product

5.0

Value of Product

4.7

Customer Images

Filter Reviews

Rating

1 - 3 of 3 Reviews

Sort by

Most Recent

★★★★★

Good For Drum Corps

Agamnon

4 years ago

I bought this to tape my marching snare sticks, and I love the strength. I am buying a case to provide for the ENTIRE drumline so we can get all of our sticks taped. I love the quality. It doesnt make the sticks too bulky, and doesnt add too much weight. 10/10 WILL buy again

Yes, I recommend this product.

Originally posted on [Scotch® Vinyl Color Coding Electrical Tape 35](#)

Helpful? (5) (1) Report

Quality of Product

Value of Product

★★★★★

Superior color coded vinyl electrical tape

TNTMAC

5 years ago

I tried a white electrical tape that was made in China. It didn't stick well and became brittle. (see first 2 pictures) I bought 5 rolls of color coded 3M Scotch Vinyl Electrical Tape to replace the old tape. The Scotch sticks securely to plastic and is superior. (see last picture) Scotch is the only electrical tape I will purchase!

Yes, I recommend this product.

Originally posted on [Scotch® Vinyl Color Coding Electrical Tape 35](#)

Helpful? (3) (1) Report

Quality of Product

Value of Product

★★★★★

Best tape

Randy3030

5 years ago

I've been using your tapes for decades. I don't even consider other brands anymore.

Yes, I recommend this product.

Originally posted on [Scotch® Vinyl Color Coding Electrical Tape 35](#)

Helpful? (4) (0) Report

Quality of Product

Value of Product

Legal disclaimer

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

For industrial/occupational use only. Not for consumer sale or use.

3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and other limitations, and the user must take any action required under any recall, field action, or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert.

OUR COMPANY

About 3M
3M Careers
Investor Relations
Partners & Suppliers
Sustainability / ESG
Equity and Community
Ethics & Compliance

NEWS

News Center
Press Releases

REGULATORY

SDS, RDS, More Regulatory & Compliance Information
Transport Information Search
CPSIA Certification Search
Lithium Battery UN 38.3 Test Summary Search
Transparency in Supply Chains and Modern Slavery Disclosures
US Ingredient Communication
Product Recalls

HELP

Help Center
Site Map
Where to Buy

FOLLOW US

[X](#) [in](#) [v](#) [f](#) [@](#)

3M

Legal | Privacy | HIPAA Privacy | DMCA | Accessibility Statement | Your Privacy Choices

© 3M 2024. All Rights Reserved.

The brands listed above are trademarks of 3M.