

MLG1005S75NJT25

**Applications**

Automotive Grade

AEC-Q200

AEC-Q200

**Feature**

Multilayer

Multilayer

Non-Mag Core

Non-Magnetic Core (Dielectric Ceramic)

**Series | Type**

MLG

**Status**

Production

**Brand**

TDK

**Size**

Length(L)	1.00mm $\pm$ 0.05mm
Width(W)	0.50mm $\pm$ 0.05mm
Thickness   Height	0.50mm $\pm$ 0.05mm
Recommended Land Pattern (A)	0.50mm Nom.
Recommended Land Pattern (B)	0.40mm Nom.
Recommended Land Pattern (C)	0.50mm Nom.

**Electrical Characteristics**

Inductance	75nH $\pm$ 5% at 100MHz
Rated Current	200mA
DC Resistance [Typ.]	930m $\Omega$
DC Resistance [Max.]	1.5 $\Omega$
Self Resonant Frequency [Min.]	750MHz
Self Resonant Frequency [Typ.]	1.1GHz
Q [Min.]	8 at 100MHz
Q [Typ.]	11 at 100MHz

**Other**

Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	YES
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	10000pcs
Weight	0.001g

! Images are for reference only and show exemplary products.





! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG1005S75NJT25



## Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.


! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG1005S75NJD25



## Associated Images



Dimensions in mm

! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.