

has not been replaced. Please contact your customer care center for more information.



Overview

Model Name	APC AV Network Manageable 15 Amp G Type Rack Power Filter, 120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Cord Length	2.44 meters

Physical

Net Weight	4.72 kg
Maximum Height	43.0 mm
Maximum Width	435.0 mm
Maximum Depth	240.0 mm
Shipping Weight	5.32 kg
Shipping Height	86.0 mm
Shipping Width	552.0 mm
Shipping Depth	330.0 mm
Master Carton Units	2.0
Master Carton Dimensions (Length x Width x Height)	22 x 13 x 7 inches
Master Carton Weight	11.24 kg
SCC Codes	2073130428434 9
Color	Black
Units per Pallet	36.0

Conformance

Approvals	UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$450000

UL 1449 TVSS Rating	330
---------------------	-----

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant