



FCI CONFIDENTIAL



2



TECHNICAL SPECIFICATION

CONTACT MATERIAL : COPPER ALLOY
 HOOD MATERIAL : STAINLESS STEEL
 CONTACT PLATING : GOLD OVER NICKEL
 OPERATING CURRENT : 7.5 A PER CONTACT
 CONTACT RESISTANCE : $\leq 7.3m\Omega$
 TERMINATION : CRIMP
 WIRE SIZE : AWG 20 TO 24 MAX

PACKING : 2000 PIECES SEALED TO A PLASTIC COVER IN A BOX

FCI PART NUMBER: 86303022A
 MIL PART NUMBER: M39029/63368

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.



FCIconnect.com

mat'l. code See Notes				surface \checkmark ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family DM			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM 	title FEMALE CRIMP CONTACTS FOR DM 20/24 AWG			
A	098-09-14	AB	2014-09-04	angles	.0 \pm 0.1					
				linear	.00 \pm 0.1					
				-	-	scale 10:1				
		dr	engr	chr	appd		dwg no		sheet 1 of 1	size
							C-DSUB-0206		A4	5
							type CUSTOMER Drawing			
sheet index	revision sheet	A 1								

form: A4

1

2