







PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.79	10.96	D09P24B4GV00LF	D09P24B6GV00LF
15	39.14	33.32	25.18	25.12	19.18	D15P24B4GV00LF	D15P24B6GV00LF
25	53.03	47.04	39.12	38.84	33.12	D25P24B4GV00LF	D25P24B6GV00LF
37	69.32	63.50	55.68	55.30	49.68	D37P24B4GV00LF	D37P24B6GV00LF
200 Mating cycles							500 Mating cycles

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0000

mat'l. code		surface		tolerance		projection	product family	
ltr	ecn no	dr	date	tolerances unless otherwise specified	angles		D-SUB	
H	EX-1-18884	AB	2014/09/24	±0.01	±0.01	MM	MALE CONNECTOR DELTA D ST	
J	EX-1-42817	ACJ	2021/10/18	±0.05	±0.05	MM	straight,solder type	
				±0.05	±0.05	MM	scale 2:1	
				±0.05	±0.05	MM	dwg no	
				±0.05	±0.05	MM	sheet 1 of 1	
				±0.05	±0.05	MM	size	
				±0.05	±0.05	MM	A3	
				±0.05	±0.05	MM	type	
				±0.05	±0.05	MM	Product Customer Drawing	
sheet index	revision	sheet	1					