


General Product and Reference Design Search

[Go](#)

Please enter in a search term.

VI Part Number: TFS1905A - Frequency: 1905.000000 MHz


[SAW Filter Page](#)

Specifications:

Please contact Vectron for the custom datasheet

Standard Features:

Frequency Range 70 MHz - 2.5 GHz
 Bidirectional, High Loss
 Transversely-coupled Resonator Filter
 Longitudinally- Coupled Resonator Filters
 Slanted Finger Interdigital Transducers
 Impedance Element Filters

More Information:

 [Standard Datasheet](#)

You Might Also be Interested in These Products

TFS110W SAW FILTER



 [Datasheet](#)

TFS403A SAW FILTER



 [Datasheet](#)

TFS915A SAW FILTER



 [Datasheet](#)

Keyword Search Matrix Table

ADEV	Clock & Data Recovery	Ethernet	GPS Disciplining	G-Sensitivity	High Stability
Hi-Rel TCXO	Hi-Rel OCXO	Holdover Oscillator	Jitter Cleaning	Low Jitter	Low Phase Noise
Low Aging	MEMS Oscillator	MTIE	1588	100G	OCXO Replacement
PEC Local Reference	Phase Accuracy	PLL	Rubidium Replacement	Ruggedized	Sensor Products
Shock & Vibration	Short Term Stability	Space OCXO	Stratum 3 & 3E	Synchronous Ethernet	TDD Mode
TDEV	High Temp (250°C)	Small Cell	Base Station		