







REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD



GREEN GREEN
12 10 10 10
RED RED
GREEN GREEN
12 10 10 10
RED RED

FOR P/N: E5J88-D4BHF-X-L



PC Board Layout
Component Side Shown

NOTES:

ELECTRICAL:

- VOLTAGE RATING : 125 VAC RMS.
- CURRENT RATING : 1.5 AMP.
- CONTACT RESISTANCE : 35 MILLIOHMS MAX.
- INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
- DIELECTRIC STRENGTH : 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

- HOUSING MATERIAL : PBT+30%G.F UL94V-0.
- CONTACT MATERIAL : PHOSPHOR BRONZE Ø0.46mm
- CONTACT PLATING : GOLD PLATING OVER NICKLE
- SHIELD PLATING : NICKEL PLATING OVER BRASS
- OPERATING LIFE : 750 CYCLES MIN.
- PCB RETENTION PRE-SOLDER : 1 LB MIN.
- PCB RETENTION POST-SOLDER: 10 LBS MIN.
- LED COLOR : GREEN

ENVIRONMENTAL:

- STORAGE : -40°C TO +85°C.
- OPERATION: -40°C TO +85°C.
- WAVE SOLDERING TEMPERATURE: 230~250°(3~5 SECONDS)

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

RoHS PART NUMBER: E5J88-X4B2FX-L

A-LEFT LED:G RIGHT LED:G Gold Thickness:
B-LEFT LED:G RIGHT LED:O 1-3u" 2-6u" 3-15u"
C-LEFT LED:G RIGHT LED:Y 4-30u" 5-50u"
D-LEFT LED:G+R RIGHT LED:G+R

DETACHED LISTS	MM (INCH)	DFTO Jake	DATE 10/19/05'	FULL RISE ELECTRONIC CO., LTD	
	TOLERANCES EXCEPT AS NOTED	CHKD ANNE	DATE 2008/10/20		
	MM	MFO	DATE		
	.0 ±0.20	APPLV LUMINO	DATE 2008/10/20		
	.00 ±0.15				
	.000 ±0.075			TITLE RJ45(LED)	
	ANGLES ±	MATERIAL :		STACKED GANGED JACK, 2X3	
	THIRD ANGLE PROJECTION	QT'Y :		DRAWING NO. GE5J3035-LC	
		FINISH :		/PART NO. SEE NOTE	
		SCALE : 5:3		DO NOT SCALE DRAWING	
				SHEET 1 OF 1	