

A

B

C





D

A

B


C

D







NOTES:


- MATERIALS:  
UPPER / LOWER COVER - HIGH TEMPERATURE NYLON;  
TERMINAL HOUSING - HIGH TEMPERATURE NYLON;  
STRAIN RELIEF - NYLON;  
LOCKING SPRING - HIGH TEMPERATURE NYLON;  
CODING KEY - HIGH TEMPERATURE NYLON - COLOR: RED  
TERMINAL BARREL - HIGH CONDUCTIVE Cu Alloy;  
TERMINAL BLADES - HIGH CONDUCTIVE Cu Alloy.
- ALL PLASTICS UL94-V0 RATED.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS






SCALE 1:1

spec ref		SEE NOTES			dr Jackie Huang		2013/08/07		projection 	MM 	size A3		scale 2:1		
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED			eng Jackie Huang		2013/09/09				ecn no ELX-DG-15763-1				
ISO 406 ISO 1101					chr -		-								
					appr Pei-Ming Zheng		2013/09/09		product family -				rel level Released		
surface  ISO 1302		linear	0.X ±0.50			title PWR TWINBLADE I/O right angle cable connector				dwg no 10126868				rev B	
			0.XX ±0.25												
			0.XXX ±0.10			www.fci.com		cat. no. -		Product - Customer Drw				sheet 1 of 3	
angular		0° ±2°													



PART NUMBER	INSTANCE DESCRIPTION	TOOLED
10126868-001LF	25 mm <sup>2</sup> - version	YES
10126868-002LF	16 mm <sup>2</sup> - version	YES






10	TERMINAL HOUSING	1
9	STRAINRELIEF	1
8	SCREW, HEX SKT CTRSUNK HD, M3X16	1
7	NUT, HEXAGON THIN, M3	1
6	LOCKING SPRING	1
5	COVER TOP	1
4	COVER BOTTOM	1
3	CODING KEY	1
2	Ass'y Terminal(short)	1
1	Ass'y Terminal(long)	1
INDEX NO.	TITLE 1	QTY

dr	Jackie Huang	2013/08/07	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2
eng	Jackie Huang	2013/09/09			ecn no	ELX-DG-15763-1		
chr	-	-						
appr	Pei-Ming Zheng	2013/09/09	product family		-	rel level		Released
	title	PWR TWINBLADE I/O right angle cable connector			dwg no	10126868		rev  B
www.fci.com	cat. no.	-	Product - Customer Drw				sheet 2 of 3	

# 4 POSITIONS OF CODING



dr	Jackie Huang	2013/08/07	projection 		size	A3	scale	3:2
eng	Jackie Huang	2013/09/09			ecn no	ELX-DG-15763-1		
chr	-	-			rel level			Released
appr	Pei-Ming Zheng	2013/09/09	product family		-			
	title		PWR TWINBLADE I/O		dwg no		rev	
			right angle cable connector		10126868		B	
	www.fci.com		cat. no.		Product - Customer Drw		sheet 3 of 3	

Copyright FCI.