


CUSTOMER PRINT



PART NUMBER: SF698X-XPG-5XX

MFG. ENG.	APPROVED BY:	DATE:	QA	APPROVED BY:	DATE:

- NOTES:
1. CRIMP CONTACTS SUPPLIED UNASSEMBLED.
 2. REFER TO DRAWING HPSFMISTD FOR CONTACT PATTERNS.
 3. DIMENSIONS ARE REFERENCE ONLY, IN INCHES [mm], WITHIN ±0.015 UNLESS OTHERWISE NOTED.



FACE VIEW
SF6982-18PG-520 SHOWN




CABLE-END CONNECTOR PART NUMBERS:

S F 6 9 8 X - X P G - 5XX


BACKSHELL KIT:
520 = BACKSHELL WITH
0.220 [5.6] GROMMET I.D.
530 = BACKSHELL WITH
0.330 [8.4] GROMMET I.D.

OF CONTACTS: 9 - 18

CONTACTS STYLE:
0 = CRIMP
2 = SOLDER



BACKSHELL KIT
MAT'L: THERMOPLASTIC SHELL & STRAP,
ELASTOMERIC GROMMET,
STAINLESS STEEL SCREWS



WIRING VIEW
SF6982-18PG-520 SHOWN
WITHOUT BACKSHELL

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

0A		PNK	2-8-18		DRAWING CREATED PER PDR17006						
REV.		INIT.		DATE		DESCRIPTION					
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.					ORIG. DRAWN BY:		DATE:		conxall 601 E. WILDWOOD VILLA PARK, IL 60181		
					PNK		2-8-18				
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16					CHECKED BY:		APPROVED BY:				
▷ - CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX					TITLE:		CABLE-END CONNECTOR 9-18 #26 PIN CONTACTS SHIELDED MINI-CON-X STANDARD PRODUCT				
					SCALE		SIZE		SHEET		CUSTOMER:
					NTS		B		1 OF 1		
					FILE:		DIRECTORY:		PART NUMBER:		
					SF698X-XPG-5XX_CD		SLW		SF698X-XPG-5XX		
									REV 0A		