

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight bulkhead cable jack (female)
24_BNC-50-3-33/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration	
Gender	Standard
jack	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data	
Weight	0.0167 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	soldered

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight bulkhead cable jack (female)

24_BNC-50-3-33/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22641923	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22641923	24_BNC-50-3-33/133_NE	Single

Suitable cables	
Cable group	Y5 - 3 mm / 50 Ohm
	Y17 - 3 mm / 50 Ohm
	Y12 - 3 mm / 50 Ohm

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543150	74_Z-0-3-4	Trimming tool
22544616	74_Z-0-0-66	Locator
22544558	74_Z-0-0-59	Support
22544557	74_Z-0-0-58	Assembly tool
22544517	74_Z-0-0-56	Gauges
23024588	74_Z-0-0-442	Soldering tool
22544282	74_Z-0-0-35	Gauges
22643028	74_Z-0-0-164	Trimming tool
22643029	74_Z-0-0-157	Cable stripping tool

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2664 / Date of publication: 11.07.2025 / uncontrolled copy