Your Expert Partner for **Human Machine Interfaces**

Switching element

84-8511.6320



https://www.eao.com/component/84-8511.6320/en...

Downloaded from Arrow.com.

Your product:



84-8511.6320
Switching element

OPERATING-/INDICATION PART

Illumination colour: Blue

ELECTRICAL CHARACTERISTICS

Switching voltage and switching current:

Voltage	42 VAC/DC
Current	100 mA
Power	max. 2 W

Contacts: 1 NO

Forward voltage:

Operating voltage: 12 V DC ±10 %

Operation current: 10 mA

Switching rating: 42 V AC/DC @ 0,1 A

Electric strength: 500 VAC, 50 Hz, 1 minute according to DIN IEC 60512-2

MECHANICAL CHARACTERISTICS

Terminal: Plug-in terminal, 2.8 x 0.8 mm

Contact material: Gold-plated silver

Switching system: Short-travel element

Switching system: Short-travel snap-action switching system with two independent contact points and tactile operation
Guarantees reliable switching even of very light loads. Fitted with 1 normally open contact

Mechanical lifetime: ≥1 Mil. cycles of operation

Operating force: 4.5 N ±1 N (measured at the lens)

Operating Travel: ca. 0.5 mm

Weight: 0.007 kg

Downloaded from Arrow.com.

AMBIENT CONDITION

IP Protection:	IP40 rear side, standard version, IP67 rear side, fully sealed version, with mounted actuator only.
Operating temperature:	– 25 °C ... + 70 °C
Storage temperature:	– 40 °C ... + 85 °C
Shock resistance:	Max. 100 m / s^2, pulse width, 3-axis (sinusoidal EN IEC 60068-2-27)
Vibration resistance:	Max. 50 m / s^2 from 10 Hz ... 500 Hz, 10 cycles, 3-axis (sinusoidal EN IEC 60068-2-6)


CERTIFICATE

Approbations:	UL
REACH:	REACH compliant
RoHS:	RoHS compliant

OTHER

Short Description:	Switching element, Short-travel element, 42 V AC/DC @ 0,1 A, Gold-plated silver, 1 NO, Plug-in terminal, 2.8 x 0.8 mm
Material:	Plastic
Hints:	LED and built-in resistor included Standard version: Cable length 300 mm Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67) Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occure, the plugs may become loose Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED Operating voltage: UL max. 35 VDC – Class 2 For use on a flat surface of a Type 4X enclosure – FOR INDOOR USE ONLY
Wiring diagrams:	

Downloaded from Arrow.com.



Downloaded from Arrow.com.